

Item description/product images



Description

Material, version:

Robust metal housing, chromium-plated

Note:

Standard clamping shank \varnothing 8h6

Measuring range 10 mm

Scale graduation 0.01 mm

Spindle travel 1 mm per revolution of large pointer

Housing \varnothing 58 mm

Rotation counter

Tolerance marks

Overview of items

Order No.	Version
32540-01	dial gauge
32540-012	dial gauge with calibration certificate