

Item description/product images



Description

Material:

Frame polyamide PA66 GF25 V-0.

Elastomer plate EPDM, ozone resistant acc. to DIN 53509, Stage 0 (best stage). Seal TPE TPV.

Version:

Black.

Note:

The cable gland plates are suitable for leading through cables without plugs (non-assembled lines). Cables, wires, hoses, pneumatic and hydraulic lines can be routed through.

The lines can be inserted without piercing. The elastomer plate adapts to the cables and provides optimum sealing and strain relief. Unused ducts remain securely closed and sealed.

Available with different glands or as a blind plate.

Rating IP66.

Certificates / standards met: UL 514B UL / CSA-File E140310

Temperature range:

-30 °C to +100 °C

Assembly:

For mounting cutouts 36 x 112 mm.

The cable gland plates can be snapped into the cut-out without the use of tools. (for a sheet thickness of 1.5 - 2 mm).

For sheets thicker than 2 mm or applications that require screwing, the cable gland plates can be fastened through holes using M5 screws.


Drawing reference:

1) mounting cutout

© norelem www.norelem.com



Drawings



Overview of items

Order No.	Max. No. of ducts	For cables
	or duoto	No. x cable Ø
84102-241101	11	4x3-6,5/4x5-9,2/3x14-20
84102-241201	12	12x8-12
84102-241301	13	2x3-5,5/6x4,1-8,1/4x9-14/1x14-20
84102-241401	14	6X3-6,5/4X5-9,2/4X9,6-15,9
84102-241701	17	17X5-9,2
84102-241702	17	11X3-6,5/1X4,1-8,1/5X8-12,5
84102-242201	22	16X3-6,5/4X5-9,2/2X8-12,5
84102-242302	23	23X4,1-8,1
84102-242901	29	29X3-6,5
84102-240000	-	-