#### tem description/product images



## Description

#### Material:

Tailstock aluminium. Centres and guides steel.

#### Version:

Tailstock hard-coated. Centres and guides nitro-carburised.

### Note:

The tailstock consists of two halves with a fixed and a movable centre. The movable centre is spring-loaded and can be locked. The centres can be exchanged as required (centres for tailstocks 34024-06).

Suitable for optical measurements on projectors. Individually adjustable using the column guides and clamped using grub screws. Can be attached to the measuring table using clamping claws.

5 5 7 5

Clamping spans of 0-210 mm are possible.

D min. and D max. refer to the workpiece being measured.

## **On request:**

Tailstock and baseplate single.

#### Accessory:

Centres 34024-06.

#### Drawings





Overview of items

# Overview of items

## Tailstock, aluminium, with centre height 75 mm

Order No.	В	B1	B2	D min.	D max.	D1	D2	D3	D4	H	H1	H2	L	L1	L2	L3
34024-05-114370	120	90	25	0	14,5	15	29,9	14,8	10	75	95	25	370	75	80	88,3