


Descrizione articolo/immagini prodotto





Descrizione

Materiale:



Acciaio da bonifica.

Versione:


trattato termicamente e brunito.



Istruzioni di installazione:

*Perno di bloccaggio*

Disegni



Sintesi articoli

N. ordine	Forma	B	B1	D	G	H	H1	H2	H3	J	L	L1	L2	Forza di bloccaggio N	Coppia di serraggio Nm
04570-0806	A	25	10	6	M8	6	15	7	1,6	3	35	24,5	10	7000	25
04570-1008	A	30	11	6	M10	8	19	7	2	4	43	29	12	8500	50
04570-1209	A	35	12	8	M12	9	23	10	2,3	5	54	37	16	20000	90
04570-1610	A	40	14	10	M16	10	25	10	3,2	6	65	45	20	40000	200
04570-0825	B	25	10	6	M8	15	25	7	1,6	3	32	21,5	10	7000	25
04570-1032	B	30	11	6	M10	19	32	7	2	4	40	26	12	8500	50
04570-1238	B	35	12	8	M12	23	38	10	2,3	5	50	33	16	20000	90
04570-1645	B	40	14	10	M16	25	45	10	3,2	6	60	40	20	40000	200