

## Item description/product images

**Description****Note:**

Gauge unit suitable for measuring concentricity, run-out and perpendicularity. The robust design allows the unit to be used in the workshop and metrology room. A swivel contact roller simplifies positioning of the workpiece. The light sliding guides allow the dial gauges to be placed anywhere.

**Technical data:**

Inspection range  $\varnothing$  5 mm to  $\varnothing$  35 mm

Roller spacing min. 29 mm.

Carriage travel max. 100 mm.

Contact roller thrust is adjustable.


Gear driven rollers.

Roller precision: parallelism and coaxialism of both rollers max. 2  $\mu$ m.

Base plate granite:

300 mm x 130 mm x 25 mm

## Drawings



Overview of items

Order No.	Item
32501-01	Concentricity Gauge