

Item description/product images



Description

Product description:

The thermoset star grip is distinguished by its closed grip contour. The contact surface of the protruding steel bush is vertical to the thread axis and ensures a firm screw connection.

Material:

Thermoset PF 31.

Steel grade 5.8 or stainless steel 1.4305.

Version:

Thermoset black, high-gloss polished.

Metal parts trivalent blue passivated steel or bright stainless steel.

Advantages:

Wear resistant contact surface

Closed grip contour

On request:


Form H: bush with blind hole

Drawing reference:

Form K: tapped bush

Form L: external thread

Drawings



Overview of items

Star grips plastic with protruding steel bush

Overview of items

Order No.	Component material	Form	D	D1	D2	H	H2	H3	L	T
06209-01-23206	0.0068	K	M6	32	13,5	23	13	9,5	-	12
06209-01-24006	0.0068	K	M6	40	13,5	25	13	10	-	12
06209-01-24008	0.0068	K	M8	40	13,5	25	13	10	-	12
06209-01-25008	0.0068	K	M8	50	19	32	17	12	-	17
06209-01-25010	0.0068	K	M10	50	19	32	17	12	-	17
06209-01-26310	0.0068	K	M10	63	19	40	20	15	-	17
06209-01-26312	0.0068	K	M12	63	19	40	20	15	-	17
06209-01-33206	280 mm / 30M10 / 20M8 Detent lever	K	M6	32	13,5	23	13	9,5	-	12
06209-01-34006	280 mm / 30M10 / 20M8 Detent lever	K	M6	40	13,5	25	13	10	-	12
06209-01-34008	280 mm / 30M10 / 20M8 Detent lever	K	M8	40	13,5	25	13	10	-	12
06209-01-35008	280 mm / 30M10 / 20M8 Detent lever	K	M8	50	19	32	17	12	-	17
06209-01-35010	280 mm / 30M10 / 20M8 Detent lever	K	M10	50	19	32	17	12	-	17
06209-01-36310	280 mm / 30M10 / 20M8 Detent lever	K	M10	63	19	40	20	15	-	17
06209-01-36312	280 mm / 30M10 / 20M8 Detent lever	K	M12	63	19	40	20	15	-	17
06209-01-43206X10	0.0068	L	M6	32	13,5	23	13	9,5	10	-
06209-01-43206X15	0.0068	L	M6	32	13,5	23	13	9,5	15	-
06209-01-43206X20	0.0068	L	M6	32	13,5	23	13	9,5	20	-
06209-01-43206X25	0.0068	L	M6	32	13,5	23	13	9,5	25	-
06209-01-43206X30	0.0068	L	M6	32	13,5	23	13	9,5	30	-
06209-01-44008X15	0.0068	L	M8	40	13,5	25	13	10	15	-
06209-01-44008X20	0.0068	L	M8	40	13,5	25	13	10	20	-
06209-01-44008X25	0.0068	L	M8	40	13,5	25	13	10	25	-
06209-01-44008X30	0.0068	L	M8	40	13,5	25	13	10	30	-
06209-01-44008X40	0.0068	L	M8	40	13,5	25	13	10	40	-
06209-01-44008X50	0.0068	L	M8	40	13,5	25	13	10	50	-
06209-01-45010X20	0.0068	L	M10	50	19	32	17	12	20	-
06209-01-45010X25	0.0068	L	M10	50	19	32	17	12	25	-
06209-01-45010X30	0.0068	L	M10	50	19	32	17	12	30	-
06209-01-45010X40	0.0068	L	M10	50	19	32	17	12	40	-
06209-01-45010X50	0.0068	L	M10	50	19	32	17	12	50	-
06209-01-45010X60	0.0068	L	M10	50	19	32	17	12	60	-
06209-01-46312X20	0.0068	L	M12	63	19	40	20	15	20	-
06209-01-46312X25	0.0068	L	M12	63	19	40	20	15	25	-
06209-01-46312X30	0.0068	L	M12	63	19	40	20	15	30	-
06209-01-46312X40	0.0068	L	M12	63	19	40	20	15	40	-
06209-01-46312X50	0.0068	L	M12	63	19	40	20	15	50	-
06209-01-46312X60	0.0068	L	M12	63	19	40	20	15	60	-
06209-01-53206X10	280 mm / 30M10 / 20M8 Detent lever	L	M6	32	13,5	23	13	9,5	10	-
06209-01-53206X15	280 mm / 30M10 / 20M8 Detent lever	L	M6	32	13,5	23	13	9,5	15	-
06209-01-53206X20	280 mm / 30M10 / 20M8 Detent lever	L	M6	32	13,5	23	13	9,5	20	-
06209-01-53206X25	280 mm / 30M10 / 20M8 Detent lever	L	M6	32	13,5	23	13	9,5	25	-
06209-01-53206X30	280 mm / 30M10 / 20M8 Detent lever	L	M6	32	13,5	23	13	9,5	30	-
06209-01-54008X15	280 mm / 30M10 / 20M8 Detent lever	L	M8	40	13,5	25	13	10	15	-
06209-01-54008X20	280 mm / 30M10 / 20M8 Detent lever	L	M8	40	13,5	25	13	10	20	-
06209-01-54008X25	280 mm / 30M10 / 20M8 Detent lever	L	M8	40	13,5	25	13	10	25	-
06209-01-54008X30	280 mm / 30M10 / 20M8 Detent lever	L	M8	40	13,5	25	13	10	30	-
06209-01-54008X40	280 mm / 30M10 / 20M8 Detent lever	L	M8	40	13,5	25	13	10	40	-
06209-01-54008X50	280 mm / 30M10 / 20M8 Detent lever	L	M8	40	13,5	25	13	10	50	-
06209-01-55010X20	280 mm / 30M10 / 20M8 Detent lever	L	M10	50	19	32	17	12	20	-
06209-01-55010X25	280 mm / 30M10 / 20M8 Detent lever	L	M10	50	19	32	17	12	25	-
06209-01-55010X30	280 mm / 30M10 / 20M8 Detent lever	L	M10	50	19	32	17	12	30	-
06209-01-55010X40	280 mm / 30M10 / 20M8 Detent lever	L	M10	50	19	32	17	12	40	-
06209-01-55010X50	280 mm / 30M10 / 20M8 Detent lever	L	M10	50	19	32	17	12	50	-
06209-01-55010X60	280 mm / 30M10 / 20M8 Detent lever	L	M10	50	19	32	17	12	60	-
06209-01-56312X20	280 mm / 30M10 / 20M8 Detent lever	L	M12	63	19	40	20	15	20	-
06209-01-56312X25	280 mm / 30M10 / 20M8 Detent lever	L	M12	63	19	40	20	15	25	-
06209-01-56312X30	280 mm / 30M10 / 20M8 Detent lever	L	M12	63	19	40	20	15	30	-
06209-01-56312X40	280mm / 20M8 / 20M8	L	M12	63	19	40	20	15	40	-
06209-01-56312X50	280mm / 20M8 / 20M8	L	M12	63	19	40	20	15	50	-
06209-01-56312X60	280mm / 20M8 / 20M8	L	M12	63	19	40	20	15	60	-

