

Item description/product images



Description

Material:

Knobs thermoset PF 31.

Rod steel or stainless steel 1.4305.

Version:

Thermoset black, high-gloss polished.

Steel black oxidised, blue passivated or bright stainless steel

Drawings



Overview of items

Order No.	Main material	Surface finish body	Form	D	D1	D2	L	L1	L2
06360-708X35	steel	black oxidised	B	8	M6	23	35	9	60
06360-708X50	steel	black oxidised	B	8	M6	23	50	9	60
06360-708X65	steel	black oxidised	B	8	M6	23	65	9	60
06360-710X50	steel	black oxidised	B	10	M8	26	50	13	70
06360-710X65	steel	black oxidised	B	10	M8	26	65	13	70
06360-710X80	steel	black oxidised	B	10	M8	26	80	13	70
06360-710X100	steel	black oxidised	B	10	M8	26	100	13	70
06360-712X65	steel	black oxidised	B	12	M10	35	65	15	85
06360-712X80	steel	black oxidised	B	12	M10	35	80	15	85
06360-712X100	steel	black oxidised	B	12	M10	35	100	15	85
06360-712X125	steel	black oxidised	B	12	M10	35	125	15	85
06360-714X80	steel	black oxidised	B	14	M12	35	80	16	85
06360-714X100	steel	black oxidised	B	14	M12	35	100	16	85
06360-714X125	steel	black oxidised	B	14	M12	35	125	16	85
06360-714X160	steel	black oxidised	B	14	M12	35	160	16	85
06360-2708X35	steel	blue-passivated	B	8	M6	23	35	9	60
06360-2708X50	steel	blue-passivated	B	8	M6	23	50	9	60
06360-2708X65	steel	blue-passivated	B	8	M6	23	65	9	60
06360-2710X50	steel	blue-passivated	B	10	M8	26	50	13	70
06360-2710X65	steel	blue-passivated	B	10	M8	26	65	13	70
06360-2710X80	steel	blue-passivated	B	10	M8	26	80	13	70
06360-2710X100	steel	blue-passivated	B	10	M8	26	100	13	70
06360-2712X65	steel	blue-passivated	B	12	M10	35	65	15	85
06360-2712X80	steel	blue-passivated	B	12	M10	35	80	15	85
06360-2712X100	steel	blue-passivated	B	12	M10	35	100	15	85
06360-2712X125	steel	blue-passivated	B	12	M10	35	125	15	85
06360-2714X80	steel	blue-passivated	B	14	M12	35	80	16	85
06360-2714X100	steel	blue-passivated	B	14	M12	35	100	16	85
06360-2714X125	steel	blue-passivated	B	14	M12	35	125	16	85
06360-2714X160	steel	blue-passivated	B	14	M12	35	160	16	85
06360-1708X35	stainless steel	bright	B	8	M6	23	35	9	60
06360-1708X50	stainless steel	bright	B	8	M6	23	50	9	60
06360-1708X65	stainless steel	bright	B	8	M6	23	65	9	60
06360-1710X50	stainless steel	bright	B	10	M8	26	50	13	70
06360-1710X65	stainless steel	bright	B	10	M8	26	65	13	70
06360-1710X80	stainless steel	bright	B	10	M8	26	80	13	70
06360-1710X100	stainless steel	bright	B	10	M8	26	100	13	70
06360-1712X65	stainless steel	bright	B	12	M10	35	65	15	85
06360-1712X80	stainless steel	bright	B	12	M10	35	80	15	85

Overview of items

Order No.	Main material	Surface finish body	Form	D	D1	D2	L	L1	L2
06360-1712X100	stainless steel	bright	B	12	M10	35	100	15	85
06360-1712X125	stainless steel	bright	B	12	M10	35	125	15	85
06360-1714X80	stainless steel	bright	B	14	M12	35	80	16	85
06360-1714X100	stainless steel	bright	B	14	M12	35	100	16	85
06360-1714X125	stainless steel	bright	B	14	M12	35	125	16	85
06360-1714X160	stainless steel	bright	B	14	M12	35	160	16	85