

## Item description/product images



## Description

**Material:**

Housing steel plate.  
Wheels PA 6.

**Version:**


Housing press formed.  
Double ball bearing with ball shield in the castor head.  
Plain bearings in the wheels.

**Note:**


The PA 6 wheels have a low rolling resistance, are non-corroding, resist abrasion and are particularly shock and impact proof.

## Drawings

swivel castor  
with "stop-fix"



## Drawings



## Overview of items

Order No.	Item	Version 1	Wheel bearing	A	B	B1	B2	B3	D	D1	H	L	L1	R	Permissible load kg
95034-075322	Swivel castor	with stop-fix locking system	plain bearing	35	32	60	-	85	75	9	98	100	80	72,5	200
95034-100372	Swivel castor	with stop-fix locking system	plain bearing	35	37	60	-	85	100	9	125	100	80	85	200
95034-125402	Swivel castor	with stop-fix locking system	plain bearing	40	40	60	-	85	125	9	150	100	80	102,5	200
95034-150502	Swivel castor	with stop-fix locking system	plain bearing	60	50	80	75	110	150	11	190	140	105	135	400