

Item description/product images



Description

Material:

1.1274 spring steel (0.005 is 1.4301 stainless steel).

Version:

Spring hard, cold rolled

Note:

These feeler gauges are supplied in a practical dispenser.

They are used for adjusting, aligning and as shims for tools, workpieces, forms etc, checking tolerances, controlling and adjusting guides, print rollers, profile templates and many other applications.

Overview of items

Order No.	thickness	strip width (mm)	length (m)	thickness tolerance mm
96382-0005	0,005	12,7	2	±0,001
96382-0010	0,01	12,7	2	±0,002
96382-0020	0,02	12,7	2	±0,002
96382-0030	0,03	12,7	2	±0,002
96382-0040	0,04	12,7	2	±0,003
96382-0050	0,05	12,7	2	±0,003
96382-0100	0,1	12,7	2	±0,004
96382-0200	0,2	12,7	2	±0,006
96382-0300	0,3	12,7	2	±0,007