

Item description/product images

**Description****Material:**

Stainless steel 1.4401.

Version:

Bright.

Grip polished.

Note:

Quarter-turn lock with T-grip. For right or left mounting with 90° closing. The quarter-turn lock can be installed pre-assembled. Supplied with standard stainless-steel nut. The lockable quarter-turn locks are each supplied with 2 keys. Rating IP65.

Please order required tongue version separately. Every tongue can be combined with this housing.

The locks have a single key system, i.e. they can all be opened using the same key (cylinder lock 1333).

*Dimension A results from the combination of the quarter turn lock and the tongue and is specified with the matching tongues.

On request:


Available for door thickness 20 and 40 mm.

Accessory:

Keys for latches and locks 05586.

Tongue for stainless steel quarter-turn lock 05566-07.

Drawings



Overview of items

Order No.	Actuation	D	H
05593-01-1186	T-Grip	32	18
05593-01-2186	lockable T-grip	32	18