

Item description/product images



Description

General:

General: multi-purpose grease for lubricating plain and rolling bearings with a high load

Multi-purpose grease 97907-10-10400:

For lubricating plain, rolling and spherical bearings, splined shafts, quick-release axles, threaded spindles and sliding surfaces of all types with a normal load and at all glide velocities that are usual for lubrication. Waterproof and free from acid. Labelling acc. to DIN 51502 K2K-30.

High-temperature grease 97907-10-20400:

For lubricating plain and rolling bearings with high temperatures, e.g. in paint curing ovens, industrial dryers, smelting converters, casting ladles, heating systems, hot-air fans, charging cranes, vulcanisation systems or electric motors. Labelling acc. to DIN 51502 KP2N-30.

Multi-purpose grease 97907-10-10500:

For lubricating rolling and plain bearings with a high load. Lubricating grease for

vehicles, construction machines and agricultural machines.

Worked penetration: 265–295 1/10 mm Water resistance: DIN ISO 51807/T1, 1–90

Corrosion protection: DIN 51802, degree of corrosion 0

Soap basis: LI-12-hydroxystearate

Base oil viscosity at 40°C: DIN 51562, ca. 135 mm²/s

Suitable for two-hand grease guns.

Overview of items

Order No.		Container	Working temperature	NLGI Class	Dropping point °C
97907-10-10400	Multi-purpose grease	400 g DIN 1284 grease cartridge	-30 °C to 120 °C	2	>190
97907-10-20400	High-temperature grease	400 g DIN 1284 grease cartridge	-35 °C to 150 °C	2	>220
97907-10-10500	Multi-purpose grease	500 g screw-in cartridge	-30 °C to 120 °C	2	180

© norelem www.norelem.com