

Item description/product images



Description





**Material:**  
Carbon steel.

**Version:**  
Hardened, black oxidised.


**Note:**  
The desired clamping force can be set by using the set screw to alter the torque. The handle snaps 15° when the set torque is achieved.

**Note:**  
Ensure that the handle is set to snap horizontally.


Drawings



Drawings




Pull Clamps 04400-3240...




If clamping force is 900 N, Load-Setting Distance will be 5 mm. Hand force will be 120 N.


Pull Clamps 04400-4050...




Swing Clamps 04366-...3232




Swing Clamps 04366-...4540



Side Clamps 04565-0500  
04565-0501



Side Clamps 04565-0800  
04565-0801



Note:  
The above performance curves apply to degreased clamps

## Overview of items

Order No.	A	B	C	D	E	F	G	H	J	K	Hand force FH N
06357-05090	89,5	60	13	18,5	6,5	8	12	5,5	M5	M5x16	0-150
06357-06119	119	84	15	23	8	10	14	6,5	M6	M6x20	0-200