


## 商品描述/产品说明



作用力示意图



## 产品说明


材料:

偏心轮材质为调质钢 1.7220, 压板材质为调质钢 1.1191。

规格:

黑色氧化处理。

图纸



## 04350 偏心夹具,中端夹紧



## 商品概述

订货号	L	L1	L2	В	S	H1 max.	H2	D	D1	SW
04350-08	104±2	39	37	20	12	28	74	M8	25	13
04350-10	123±2	49	46	25	16	39	92	M10	30	17
04350-12	146±3	61	58	32	20	49	120	M12	30	19