

商品描述/产品说明



产品说明

材料: 调制钢。

规格:

经硬化 (33-39 HRC) 和黑色氧化处理。

提示:


定心夹具实现在孔内定中心和夹紧工件。 通过楔面实现较大的夹持力。 带下拉效应的定心夹具。

图纸提示:

尺寸 H 指 ≥D 时的高度。

1) O 型圈


















提示: 夹紧过程中夹持力应正好作用在孔壁上。






© norelem www.norelem.com 1/2 图纸







商品概述

订货号	类型	D=螺纹	D	D	Н	H1	L	SW	夹紧力	锁紧扭矩
				max.					max. kN	Nm
03164-10804	Α	M4x12	8	10,3	5,5	0,9	7,3	2,5	0,9	2,1
03164-11005	Α	M5X15	10	12,3	6,4	1,1	9,1	3	1,5	4,3
03164-11206	Α	M6X18	12	16,3	8,6	1,3	11,2	4	2,1	7,3
03164-11608	Α	M8X25	16	22	11,5	1,6	16,2	5	4	18