

商品描述/产品说明



产品说明

材料：
渗碳钢制导向螺栓 1.7139。


规格：
经渗碳硬化处理。

提示：
钢制导向螺栓是高要求制造工艺中精确导向任务的完美解决方案。导向螺栓可在各种应用中提供最大的稳定性、耐用性和精度。


导向螺栓设计坚固，即使在高负荷情况下也能确保可靠的导向。其用于安全、精确地定位工具和模具，以实现高精度的加工结果。

导向螺栓的设计可实现平滑移动和校准，提高制造流程的效率和质量。精密的加工确保了其在整个使用寿命内性能稳定。

3+1 原则确保两个半模的正确安装。安装 3 个直径较大的导向元件和 1 个直径较小的导向元件。



图纸



商品概述

订货号	D	D1	L	L1	L2
21597-10-08040	8	10	40	3	4
21597-10-08050	8	10	50	3	4
21597-10-08060	8	10	60	3	4
21597-10-08080	8	10	80	3	4
21597-10-08100	8	10	100	3	4
21597-10-09040	9	12	40	3	4
21597-10-09060	9	12	60	3	4
21597-10-09080	9	12	80	3	4
21597-10-09100	9	12	100	3	4
21597-10-09120	9	12	120	3	4
21597-10-10040	10	12	40	3	4
21597-10-10060	10	12	60	3	4
21597-10-10080	10	12	80	3	4
21597-10-10100	10	12	100	3	4
21597-10-10120	10	12	120	3	4
21597-10-10140	10	12	140	3	4
21597-10-10160	10	12	160	3	4
21597-10-12040	12	16	40	6	5
21597-10-12060	12	16	60	6	5
21597-10-12080	12	16	80	6	5
21597-10-12100	12	16	100	6	5

商品概述

订货号	D	D1	L	L1	L2
21597-10-12120	12	16	120	6	5
21597-10-12140	12	16	140	6	5
21597-10-12160	12	16	160	6	5
21597-10-12180	12	16	180	6	5
21597-10-12200	12	16	200	6	5
21597-10-14060	14	18	60	8	5
21597-10-14080	14	18	80	8	5
21597-10-14100	14	18	100	8	5
21597-10-14120	14	18	120	8	5
21597-10-14140	14	18	140	8	5
21597-10-14160	14	18	160	8	5
21597-10-14180	14	18	180	8	5
21597-10-14200	14	18	200	8	5
21597-10-14220	14	18	220	8	5
21597-10-14240	14	18	240	8	5
21597-10-15060	15	18	60	8	5
21597-10-15080	15	18	80	8	5
21597-10-15100	15	18	100	8	5
21597-10-15120	15	18	120	8	5
21597-10-15140	15	18	140	8	5
21597-10-15160	15	18	160	8	5
21597-10-15180	15	18	180	8	5
21597-10-15200	15	18	200	8	5
21597-10-15220	15	18	220	8	5
21597-10-15240	15	18	240	8	5
21597-10-16040	16	20	40	8	5
21597-10-16060	16	20	60	8	5
21597-10-16080	16	20	80	8	5
21597-10-16100	16	20	100	8	5
21597-10-16120	16	20	120	8	5
21597-10-16140	16	20	140	8	5
21597-10-16160	16	20	160	8	5
21597-10-16180	16	20	180	8	5
21597-10-16200	16	20	200	8	5
21597-10-16220	16	20	220	8	5
21597-10-16240	16	20	240	8	5
21597-10-16300	16	20	300	8	5
21597-10-18060	18	22	60	8	7
21597-10-18080	18	22	80	8	7
21597-10-18100	18	22	100	8	7
21597-10-18120	18	22	120	8	7
21597-10-18140	18	22	140	8	7
21597-10-18160	18	22	160	8	7
21597-10-18180	18	22	180	8	7
21597-10-18200	18	22	200	8	7
21597-10-18220	18	22	220	8	7
21597-10-18240	18	22	240	8	7
21597-10-18260	18	22	260	8	7
21597-10-18280	18	22	280	8	7
21597-10-18300	18	22	300	8	7
21597-10-18320	18	22	320	8	7
21597-10-20060	20	24	60	8	7
21597-10-20080	20	24	80	8	7
21597-10-20100	20	24	100	8	7
21597-10-20120	20	24	120	8	7
21597-10-20140	20	24	140	8	7
21597-10-20160	20	24	160	8	7
21597-10-20180	20	24	180	8	7
21597-10-20200	20	24	200	8	7
21597-10-20220	20	24	220	8	7
21597-10-20240	20	24	240	8	7
21597-10-20260	20	24	260	8	7
21597-10-20280	20	24	280	8	7
21597-10-20300	20	24	300	8	7
21597-10-20320	20	24	320	8	7

商品概述

订货号	D	D1	L	L1	L2
21597-10-22080	22	26	80	15	7
21597-10-22100	22	26	100	15	7
21597-10-22120	22	26	120	15	7
21597-10-22140	22	26	140	15	7
21597-10-22160	22	26	160	15	7
21597-10-22180	22	26	180	15	7
21597-10-22200	22	26	200	15	7
21597-10-22220	22	26	220	15	7
21597-10-22240	22	26	240	15	7
21597-10-22260	22	26	260	15	7
21597-10-22280	22	26	280	15	7
21597-10-22300	22	26	300	15	7
21597-10-22320	22	26	320	15	7
21597-10-22340	22	26	340	15	7
21597-10-22360	22	26	360	15	7
21597-10-24080	24	28	80	15	7
21597-10-24100	24	28	100	15	7
21597-10-24120	24	28	120	15	7
21597-10-24140	24	28	140	15	7
21597-10-24160	24	28	160	15	7
21597-10-24180	24	28	180	15	7
21597-10-24200	24	28	200	15	7
21597-10-24220	24	28	220	15	7
21597-10-24240	24	28	240	15	7
21597-10-24260	24	28	260	15	7
21597-10-24280	24	28	280	15	7
21597-10-24300	24	28	300	15	7
21597-10-24320	24	28	320	15	7
21597-10-24340	24	28	340	15	7
21597-10-24360	24	28	360	15	7
21597-10-30100	30	36	100	15	7
21597-10-30120	30	36	120	15	7
21597-10-30140	30	36	140	15	7
21597-10-30160	30	36	160	15	7
21597-10-30180	30	36	180	15	7
21597-10-30200	30	36	200	15	7
21597-10-30240	30	36	240	15	7
21597-10-30300	30	36	300	15	7
21597-10-30360	30	36	360	15	7
21597-10-30400	30	36	400	15	7
21597-10-32100	32	36	100	15	7
21597-10-32120	32	36	120	15	7
21597-10-32140	32	36	140	15	7
21597-10-32160	32	36	160	15	7
21597-10-32180	32	36	180	15	7
21597-10-32200	32	36	200	15	7
21597-10-32240	32	36	240	15	7
21597-10-32300	32	36	300	15	7
21597-10-32360	32	36	360	15	7
21597-10-32400	32	36	400	15	7
21597-10-40160	40	48	160	15	10
21597-10-40200	40	48	200	15	10
21597-10-40240	40	48	240	15	10
21597-10-40300	40	48	300	15	10
21597-10-40360	40	48	360	15	10
21597-10-40400	40	48	400	15	10
21597-10-40420	40	48	420	15	10
21597-10-40500	40	48	500	15	10
21597-10-50160	50	58	160	15	15
21597-10-50200	50	58	200	15	15
21597-10-50240	50	58	240	15	15
21597-10-50300	50	58	300	15	15
21597-10-50360	50	58	360	15	15
21597-10-50400	50	58	400	15	15
21597-10-50500	50	58	500	15	15

商品概述

订货号	D	D1	L	L1	L2
21597-10-60280	60	58	280	15	15
21597-10-60300	60	58	300	15	15
21597-10-60340	60	58	340	15	15
21597-10-60360	60	58	360	15	15
21597-10-60400	60	58	400	15	15
21597-10-60500	60	58	500	15	15