

Item description/product images



Description

Material:

AlNiCo (aluminium, nickel, cobalt).

Version:

Bright.

Note:

Unshielded system.


Temperature range:

max. 450°C.

Assembly:

The magnets can be mounted by press-fit or gluing.

Drawings



Overview of items

Order No.	D	L	Magnetic force N
09003-0310	3 +0/-0,2	10 ±0,1	1,1
09003-0312	3 +0/-0,2	12 ±0,1	1,3
09003-0416	4 +0/-0,2	16 ±0,1	1,9
09003-0420	4 +0/-0,2	20 ±0,1	2
09003-0520	5 +0/-0,2	20 ±0,1	2,3
09003-0615	6 +0/-0,2	15 ±0,1	2,8
09003-0624	6 +0/-0,2	24 ±0,1	2,8
09003-0630	6 +0/-0,2	30 ±0,1	2,8
09003-0825	8 +0/-0,2	25 ±0,1	3,8
09003-1020	10 +0/-0,2	20 ±0,1	5
09003-1040	10 +0/-0,2	40 ±0,1	7
09003-1240	12 +0/-0,2	40 ±0,1	8
09003-1530	15 +0/-0,2	30 ±0,2	10
09003-1560	15 +0/-0,2	60 ±0,2	11
09003-3480	34 +0/-0,2	80 ±0,2	61