

Item description/product images



Description

Material:

Housing steel tube filled with steel balls.

Shaft steel tube with rubber grip or Hickory.

Inserts white nylon (grease and oil resistant).

Note:

Inserts to reorder 96614.



Overview of items

Order No.	Version 1	Head-Ø	H=Height	L=Length
96610-03001	external thread	30	110	330
96610-04001	external thread	40	115	360
96610-05001	external thread	50	120	370
96610-06001	external thread	60	145	370
96610-03002	external thread	30	110	290
96610-04002	external thread	40	115	300
96610-05002	external thread	50	120	310
96610-06002	external thread	60	145	325