

Item description/product images



Description

Material:
Polyethylene

Note for ordering:
Supplied on rolls only.

Overview of items

Order No.	Version 1	Recommended Ø	Colour	Length	G=Weight g/m
96500-007X25000	medium loading	7-15 mm	orange	250 m / on the roll	18
96500-015X20000	medium loading	15-25 mm	blue	200 m / on the roll	18
96500-025X10000	medium loading	25-50 mm	yellow	100 m / on the roll	40
96500-050X10000	medium loading	50-100 mm	red	100 m / on the roll	85
96500-100X05000	medium loading	100-200 mm	green	50 m / on the roll	100
96500-200X05000	medium loading	200-300 mm	orange	50 m / on the roll	120
96500-300X05000	medium loading	300-600 mm	white	50 m / on the roll	250
96500-007X250001	light loading	7-15 mm	orange	250 m / on the roll	14
96500-015X250001	light loading	15-25 mm	blue	250 m / on the roll	14
96500-025X100001	light loading	25-50 mm	yellow	100 m / on the roll	30
96500-050X100001	light loading	50-100 mm	red	100 m / on the roll	50
96500-080X100001	light loading	80-150 mm	red	100 m / on the roll	50
96500-150X100001	light loading	150-250 mm	black	100 m / on the roll	60
96500-005X050002	heavy loading	5-10 mm	blue	50 m / on the roll	16
96500-010X050002	heavy loading	10-20 mm	blue	50 m / on the roll	27
96500-020X050002	heavy loading	20-30 mm	blue	50 m / on the roll	40
96500-030X050002	heavy loading	30-45 mm	blue	50 m / on the roll	40
96500-045X050002	heavy loading	45-75 mm	blue	50 m / on the roll	70
96500-075X050002	heavy loading	75-100 mm	blue	50 m / on the roll	120
96500-100X050002	heavy loading	100-150 mm	blue	50 m / on the roll	140
96500-150X050002	heavy loading	150-180 mm	blue	50 m / on the roll	180
96500-180X050002	heavy loading	180-220 mm	blue	50 m / on the roll	190
96500-005X300003	very light load	5-25 mm	colourless	300 m / on the roll	8
96500-020X500003	very light load	20-50 mm	green	500 m / on the roll	13
96500-050X200003	very light load	50-90 mm	red	200 m / on the roll	20