tem description/product images



Description

Material:

Housing high-strength aluminium. Stop system steel.

Version:

Housing anodised. Stop system hardened and black oxidised.

Note:

Maintenance-free pneumatic rotary module with double actuated drive cylinder. Control by 4/2 or 5/2 directional valve. Pneumatic drive, 4-8 bar, constant, filtered (10 μ m), dried, oiled or unoiled. Compressed air connection M5. Modules of the same size can be combined with one another without adapter plates via the precise centring system by means of centring rings 20240.

The $0^{\circ} - 190^{\circ}$ rotation angle is infinitely adjustable.

Repeat accuracy ±0.01°.

Accessory:

See table for shock absorber, proximitiy switch and plug connector.



Overview of items

ľ	20060-024	4	0,94	0° - 190°	280	350	2 x 14	19
								6 bar (ccm)
				angle	load	load		per cycle at
	Order No.	Size	Driving torque			Radial	Cylinder	Air consumption

20060-024	4	26300-1210010	83000-15-020	80150-010X2000
		absorber	switch	connector
		shock	proximity	plug
Order No.	Size	Suitable	Suitable	