Item description/product images



Description

Material:

Housing and cap thermoplastic polyamide 66. Air filter polyurethane (PU foam). Dipstick zinc. O-ring NBR, Shore 70.

Version:

Housing black. Cap red. Filter mesh 50 µm. Dipstick phosphated.

Temperature range: Temperature resistant with oil up to 100°C.

On request: Min-Max markings.

Drawing reference:

Form A: without vent Form B: with vent Form C: with vent and air filter

1) O-ring
2) air filter Form C only

Drawings





Overview of items

Order No. Form A	Order No. Form B	Order No. Form C	D	D1	D2	L	L1	S min.
28048-13018	28048-23018	28048-33018	30	18	23	14	14	8