

Item description/product images

**Description****Material:**

Fibreglass reinforced thermoplastic.
Hinge pin stainless steel.

Version:

Hinge black. Pin bright.

Note:


All hinges can be supplied on request with guide tabs for the slots of aluminium profiles (slots 6, 8 and 10). They facilitate assembly, secure the hinge against rotation and make it harder wearing.

The loading values given for the hinges are non-binding reference values without consideration of safety factors and exclude any liability. The values given are for information purposes only and do not constitute a legally binding assurance of properties.

The load values have been determined under laboratory conditions. Each user must determine individually whether the hinge is suitable for the respective application.

Different materials onto which the hinges are installed and the type of mounting, weather conditions and wear can influence the determined values.

Drawings



Overview of items

Order No.	A	A1	A2	A3	A4	B	B2	D1	D2	D3	H	F1 N	F2 N
27850-2251515	52	15	15	26	26	48	28	6,6	6	14	9	625	425
27850-2251518	55,5	15	17,5	26	29,5	48	28	6,6	6	14	9	700	500
27850-2251520	61,5	15	20	26	35,5	48	28	6,6	6	14	9	700	400
27850-2251523	64,5	15	22,5	26	38,5	48	28	6,6	6	14	9	800	350
27850-2251525	69,5	15	25	26	43,5	48	28	6,6	6	14	9	800	325
27850-2251528	74,5	15	27,5	26	48,5	48	28	6,6	6	14	9	800	320
27850-2251533	83,5	15	32,5	26	57,5	48	28	6,6	6	14	9	800	240
27850-2301815	55,5	17,5	15	29,5	26	48	28	6,6	6	14	9	750	450
27850-2301818	59	17,5	17,5	29,5	29,5	48	28	6,6	6	14	9	750	500
27850-2301820	65	17,5	20	29,5	35,5	48	28	6,6	6	14	9	700	400
27850-2301823	68	17,5	22,5	29,5	38,5	48	28	6,6	6	14	9	800	350
27850-2301825	73	17,5	25	29,5	43,5	48	28	6,6	6	14	9	800	350
27850-2301828	78	17,5	27,5	29,5	48,5	48	28	6,6	6	14	9	800	350
27850-2301833	87	17,5	32,5	29,5	57,5	48	28	6,6	6	14	9	800	240
27850-2352015	61,5	20	15	35,5	26	48	28	6,6	6	14	9	700	400
27850-2352018	65	20	17,5	35,5	29,5	48	28	6,6	6	14	9	750	500
27850-2352020	71	20	20	35,5	35,5	48	28	6,6	6	14	9	750	400
27850-2352023	74	20	22,5	35,5	38,5	48	28	6,6	6	14	9	800	350
27850-2352025	79	20	25	35,5	43,5	48	28	6,6	6	14	9	800	350
27850-2352028	84	20	27,5	35,5	48,5	48	28	6,6	6	14	9	800	350
27850-2352033	93	20	32,5	35,5	57,5	48	28	6,6	6	14	9	800	240
27850-2402315	64,5	22,5	15	38,5	26	48	28	6,6	6	14	9	650	425
27850-2402318	68	22,5	17,5	38,5	29,5	48	28	6,6	6	14	9	750	500
27850-2402320	74	22,5	20	38,5	35,5	48	28	6,6	6	14	9	750	400
27850-2402323	77	22,5	22,5	38,5	38,5	48	28	6,6	6	14	9	800	350

Overview of items

Order No.	A	A1	A2	A3	A4	B	B2	D1	D2	D3	H	F1 N	F2 N
27850-2402325	82	22,5	25	38,5	43,5	48	28	6,6	6	14	9	800	350
27850-2402328	87	22,5	27,5	38,5	48,5	48	28	6,6	6	14	9	800	350
27850-2402333	96	22,5	32,5	38,5	57,5	48	28	6,6	6	14	9	800	240
27850-2452515	69,5	25	15	43,5	26	48	28	6,6	6	14	9	650	425
27850-2452518	73	25	17,5	43,5	29,5	48	28	6,6	6	14	9	750	500
27850-2452520	79	25	20	43,5	35,5	48	28	6,6	6	14	9	700	400
27850-2452523	82	25	22,5	43,5	38,5	48	28	6,6	6	14	9	800	350
27850-2452525	87	25	25	43,5	43,5	48	28	6,6	6	14	9	800	325
27850-2452528	92	25	27,5	43,5	48,5	48	28	6,6	6	14	9	800	320
27850-2452533	101	25	32,5	43,5	57,5	48	28	6,6	6	14	9	800	240
27850-2502815	74,5	27,5	15	48,5	26	48	28	6,6	6	14	9	650	425
27850-2502818	78	27,5	17,5	48,5	29,5	48	28	6,6	6	14	9	750	500
27850-2502820	84	27,5	20	48,5	35,5	48	28	6,6	6	14	9	700	400
27850-2502823	87	27,5	22,5	48,5	38,5	48	28	6,6	6	14	9	800	350
27850-2502828	97	27,5	27,5	48,5	48,5	48	28	6,6	6	14	9	800	320
27850-2502833	106	27,5	32,5	48,5	57,5	48	28	6,6	6	14	9	800	240
27850-2603318	87	32,5	17,5	57,5	29,5	48	28	6,6	6	14	9	750	500
27850-2603320	93	32,5	20	57,5	35,5	48	28	6,6	6	14	9	700	400
27850-2603323	96	32,5	22,5	57,5	38,5	48	28	6,6	6	14	9	800	350
27850-2603325	101	32,5	25	57,5	43,5	48	28	6,6	6	14	9	800	325
27850-2603328	106	32,5	27,5	57,5	48,5	48	28	6,6	6	14	9	900	320
27850-2603333	115	32,5	32,5	57,5	57,5	48	28	6,6	6	14	9	900	240