


Item description/product images



Description

Material:

Steel version:

Load ball steel.

Bearing balls steel.

Housing electro zinc-plated steel.

Cover electro zinc-plated steel.

Stainless steel version:

Load ball stainless steel.

Bearing balls stainless steel.

Housing stainless steel.

Cover aluminium.

Note:


The ball transfer units comprise a housing with integrated bearing shell, a cover, a load ball and several supporting balls. For use in measuring instruments, material conveyance in clean rooms and miniature mechanisms.

Drawing reference:

1) load ball

2) bearing balls

Drawings



Overview of items

Order No.	Form	Main material	DK	D1	D2	H	H1	L	Load rating C (N)
95180-1105	A	0.0042	4,8	13	M6	24	1	15	100
95180-1106	A	0.0042	6,4	17	M6	26	2	15	200
95180-1108	A	0.0042	7,9	18	M8	32	2	18	300
95180-1110	A	0.0042	9,6	23	M8	40	2	20	400
95180-1113	A	0.0042	12,7	28	M8	48	3,5	23	500

Overview of items

Order No.	Form	Main material	DK	D1	D2	H	H1	L	Load rating C (N)
95180-1216	B	0.0042	15,8	24	M6	32,5	4	12	700
95180-2205	B	250 m / on the roll	4,8	8	M2	8,5	1	2,5	50
95180-2206	B	250 m / on the roll	6,4	13	M3	16,5	2	6	100
95180-2208	B	250 m / on the roll	7,9	15	M4	20,5	2	8	150