



Item description/product images




downthrust clamping



vertical clamping



horizontal clamping



When mounting an attachment on the clamping cylinder, hold the shaft using a spanner to prevent turning.

Description

Material:

Cam tool steel.
Shaft and grip QT steel.
Ball knob thermoset PF 31.

Version:

Cam and shaft hardened and black oxidised.
Grip black oxidised.
Ball knob, black.


Note:

* Admissible hand force for the handle.

Accessory:

Standard handles 06355.
Screw-in handles with adjustable torque 06357.

Drawings



Overview of items

Order No.	Version 1	A min.	A max.	B	C	D	E	F	G	H	J	K	L	M	N	Clamping force N	Hand force FH N
04402-252500	without grip	25	26,7	25	23	16	10	1,7	M4 x 6	M4x6	-	15	123°	12	-	3000	150*
04402-252501	with grip	25	26,7	25	23	16	10	1,7	M4 x 6	M4x6	20	15	123°	12	69,5	3000	150*
04402-323200	without grip	32	34,5	32	30	20	13	2,5	M6 x 9	M6 x 9	-	19,5	135°	15	-	4000	200*
04402-323201	with grip	32	34,5	32	30	20	13	2,5	M6 x 9	M6 x 9	25	19,5	135°	15	103	4000	200*

