

Item description/product images

**Description****Material:**

Housing, actuator, nut and key die-cast zinc.
Flat seal rubber.

Version:

Housing and actuator chrome-plated or black powder-coated.
Key chrome-plated.

Note:

Security quarter turn lock with spring-loaded tongue. Right or left deployment. The lock can be installed pre-assembled. The fastening nut is an earthing nut with teeth one side.

Water and dust tight according to IP65.

Please order key separately. Lock can only be opened and closed with a specific key. The key can only be removed in the closed position. With an open lock the key acts as a grip.

Please order the desired tongue type separately. Every tongue can be combined with every housing.

*Dimension A results from the combination of the quarter turn lock and the tongue and is specified with the matching tongues.


Accessory:

Tongue for steel quarter-turn lock 05569.

Drawing reference:

- 1) Key can be pulled out when locked
- 2) Key cannot be pulled out when open

Drawings



Overview of items

Order No.	Surface finish body	Actuation	H	SW	Order No Key
05578-01-181	chromed	Key	18,5	27	05578-01-9
05578-01-182	powder-coated	Key	18,5	27	05578-01-9

Order No.	Item
05578-01-9	Lock Key