

Item description/product images



Description

Material:

Housing in thermoplastic polyamide.
Plastic reflector.

Version:

Housing, transparent, high mechanical stability, non-ageing, temperature resistant with oil up to 90 °C, resistant to solvents but not to alcohol or frost.
Flat seal, asbestos-free.
Reflector white.

On request:

Rubber gasket (NBR).


Drawing reference:

Form A: without reflector

Form B: with reflector

- 1) flat seal
- 2) check mark
- 3) reflector

Drawings



Overview of items

Order No.	Form	D	D1	D2	L	L1	SW	Tightening torque max. Nm
28004-120014	A	20,5	G1/4	12	8	8,5	17	5
28004-122038	A	22	G3/8	12	6,5	12	18	7
28004-128012	A	28	G1/2	16	8	12	24	15
28004-135034	A	36	G3/4	21	8,5	13,5	30	20
28004-143100	A	42	G1	30	9	16	36	25
28004-151114	A	51	G1 1/4	32	10	17	42	-
28004-158112	A	58	G1 1/2	39	10	21	50	-
28004-174200	A	74	G2	48	12	20	64	-
28004-1201415	A	20	M14X1,5	12	7,5	8	17	5
28004-1221615	A	22	M16X1,5	12	6,5	12,5	18	7
28004-1251815	A	25,5	M18X1,5	14	6	12,5	21	10
28004-1282015	A	28	M20X1,5	16	7,5	12	24	15
28004-1282215	A	28	M22X1,5	16	7,5	12,5	24	15
28004-1362615	A	36	M26X1,5	21	8,5	13,5	30	20
28004-1362715	A	36	M27X1,5	21	8,5	13,5	30	20
28004-1514015	A	51	M40X1,5	32	10	17	42	-
28004-222038	B	22	G3/8	12	6,5	12	18	7
28004-228012	B	28	G1/2	16	8	12	24	15
28004-235034	B	36	G3/4	21	8,5	13,5	30	20
28004-243100	B	42	G1	30	9	16	36	25

Overview of items

Order No.	Form	D	D1	D2	L	L1	SW	Tightening torque max. Nm
28004-251114	B	51	G1 1/4	32	10	17	42	-
28004-258112	B	58	G1 1/2	39	10	21	50	-
28004-274200	B	74	G2	48	12	20	64	-
28004-2221615	B	22	M16X1,5	12	6,5	12,5	18	7
28004-2251815	B	25,5	M18X1,5	14	6	12,5	21	10
28004-2282015	B	28	M20X1,5	16	7,5	12	24	15
28004-2282215	B	28	M22X1,5	16	7,5	12,5	24	15
28004-2362615	B	36	M26X1,5	21	8,5	13,5	30	20
28004-2362715	B	36	M27X1,5	21	8,5	13,5	30	20
28004-2514015	B	51	M40X1,5	32	10	17	42	-