

Item description/product images

**Description****Material:**

Stainless steel 1.4401.

Version:

Bright.

Note:

The secure quarter turn lock is shock and vibration-resistant acc. to DIN 43668 even under high pressing force due to a built-in restrictor element. Actuation without a suitable key is not possible. The key can be removed only in the locked position. quarter turn lock, pre-assembled. Right version = closes anti-clockwise. Left version = closes clockwise. Water and dust protected acc. to IP65 from DIN EN 60529.

Please order required tongue version separately. Every tongue can be combined with every housing.

*Dimension A results from the combination of the quarter turn lock and the tongue and is specified with the matching tongues.

Accessory:

Key 05586

Tongue for stainless steel quarter-turn lock 05566-07.


Drawing reference:

- 1) flat seal
- 2) self-locking screw

Actuation:

- a) double lug 5 mm

Drawings



Overview of items

Order No.	Version 1	Actuation	D	H
05578-02-14518	right	double lug 5 mm	30	18
05578-02-24518	left	double lug 5 mm	30	18