tem description/product images





Description

Material:

Thermoplastic. DIN 7984 screws and DIN 985 nuts steel.

Version:

Black. Screws and nuts electro zinc-plated.

Note:

Tube swivel clamps can be seamlessly rotated through 180°.

The standard size for round tubes is Ø18 mm or Ø30 mm. Use reducer sleeves 29042 if smaller tubes are to be clamped or a conversion from round to square tubes is required.

On request:

Plastic clamping levers for tightening.

Accessory:

- Reducer sleeves 29042

- Round and square tubes 29050

Note:

Tightening torque for clamping screws: M6: 10 Nm M8: 25 Nm



Drawings



Overview of items

Order No.	A	В	С	D	E	F	G	Н	K	L	N	0	Р	R	S
29036-18	18	5,3 (2x)	30	25	26,5	40	50	20	-	65	5	35	21	34	M6x18
29036-30	30	6,5 (4x)	45	40	41,5	60	75	32,5	60	100,5	7,5	75	28,5	52,5	M8x25