

Item description/product images

**Description****Material:**

Housing aluminium.

Measuring spindle stainless steel.

Version:

Measuring spindle hardened and ground.

Note:

Display rotatable by 280°

Standard holding shank Ø 8h6

Exchangeable probe

Thread M2.5

Protection class IP42

Function:

- Optional measuring system mm/inch
- PRESET

Electronics can be switched off.

6 digit LCD display.

Extra large digits.

Digit height 8.5 mm.

Max. traverse speed 1.5 m/s.

Data interface: Digimatic, Opto RS-232C, USB factory standard.

Battery life ca. 2000 hours.


Supplied with type CR2032 battery.

Accessory:

Spare CR2032 battery

order No. 32510-20.

Drawings



Overview of items

Order No.	Version	Type	A	B	Measuring range mm	Resolution mm	Precision mm	Repeat precision μm	Probe force N
32542-01	125°	Preset	78,4	53,4	25	0,001	0,005	2 ($\pm 2\text{s}$)	0,6 - 1,10
32542-02	125°	Preset	78,4	53,4	25	0,01	0,010	2 ($\pm 2\text{s}$)	0,6 - 1,10
32542-03	125°	Preset	65,9	53,4	12,5	0,001	0,005	2 ($\pm 2\text{s}$)	0,7 - 0,95
32542-04	125°	Preset	65,9	53,4	12,5	0,01	0,010	2 ($\pm 2\text{s}$)	0,65 - 0,9
32542-012	12-pin	Preset	78,4	53,4	25	0,001	0,005	2 ($\pm 2\text{s}$)	0,6 - 1,10
32542-022	12-pin	Preset	78,4	53,4	25	0,01	0,010	2 ($\pm 2\text{s}$)	0,6 - 1,10
32542-032	12-pin	Preset	65,9	53,4	12,5	0,001	0,005	2 ($\pm 2\text{s}$)	0,7 - 0,95
32542-042	12-pin	Preset	65,9	53,4	12,5	0,01	0,010	2 ($\pm 2\text{s}$)	0,65 - 0,9