tem description/product images



Description

Material:

Thermoplastic PPA (resistant to high temperatures), fibreglass reinforced. Bush, stainless steel.

Version:

Black.

Note:

This pull handle is characterised by its large size and pleasant haptics. Easy to clean due to its closed and smooth design (i.e. suitable for foodstuff production, medical technology).

Screw-on dimension "A" applies after grip assembly. In the unassembled state it may deviate through flexural stress by deforming.

Temperature range:

Continuous operating temperature acc. to IEC 216 max. 160 °C. Short-term operating temperature: max. 250 °C. Suitable for steam sterilisation (medical technology).

Assembly:

From the rear.



Overview of items

Order No.	Form	A	В	С	D	H	L	S	Т	Load capacity N
06916-01-2100054	В	100	17	10,3	M5	34	122,5	20	9	1000
06916-01-2120064	В	120	21	12,4	M6	41	146	24	12	1000

Drawings

Overview of items