


Item description/product images



Description

Material:

Cable stainless steel.

Crimp and end terminal aluminium.


Version:

Cable plastic coated.


Note:

With the retaining cable and pin ring (03199) the ball lock pins (03193, 03194 and 03196) can be secured so that they cannot be lost. An M5 screw is used to secure the retaining cable.

Application temperature: +80 °C.



Drawings



Overview of items

Order No.	Form	L	D=rope diameter
03199-0150	A	150	1,6
03199-0200	A	200	1,6
03199-0300	A	300	1,6
03199-0500	A	500	1,6
03199-1150	B	150	1,6
03199-1200	B	200	1,6
03199-1300	B	300	1,6
03199-1500	B	500	1,6

Overview of items

Order No.	Form	L	D=rope diameter
03199-2150	C	150	1,6
03199-2200	C	200	1,6
03199-2300	C	300	1,6
03199-2500	C	500	1,6