

Item description/product images



Description

Material:

Thermoset PF 31, black.

Hubs and steel parts of grip nickel-plated steel or bright 1.4305 stainless steel.

Version:

High-gloss polished.

Note:

The handwheel is supplied with the grip loose.

On request:


Other reamed hole sizes.

Drawing reference:

Form D: pilot hole

Form E: reamed hole

Drawings



Overview of items

Handwheels disc, with revolving grip

Order No.	Form	Form definition	Steel parts material	D1	D2	D3	D4	D6	D7	D8	H	H1	H2	L1	L2	L3	L4
06287-0100X06	D	pre-drilled	steel	100	6	22	20	79	M6	29	12	9	8	29,5	19	39	54,7
06287-0125X08	D	pre-drilled	steel	125	8	26	21	101	M6	34	15	9	8	34	24	46	54,7
06287-0140X08	D	pre-drilled	steel	140	8	30	25	110	M8	39	16	12	8	38,5	27	52	82,2
06287-0160X10	D	pre-drilled	steel	160	10	33	30	128	M8	43	20	12	8	41,3	30,1	57	82,2
06287-1100X10	E	with reamed hole	steel	100	10H8	22	20	79	M6	29	-	9	8	29,5	19	39	54,7
06287-1125X12	E	with reamed hole	steel	125	12H8	26	21	101	M6	34	-	9	8	34	24	46	54,7
06287-1140X14	E	with reamed hole	steel	140	14H8	30	25	110	M8	39	-	12	8	38,5	27	52	82,2
06287-1160X16	E	with reamed hole	steel	160	16H8	33	30	128	M8	43	-	12	8	41,3	30,1	57	82,2
06287-1160X18	E	with reamed hole	steel	160	18H8	33	30	128	M8	43	-	12	8	41,3	30,1	57	82,2

Overview of items

Order No.	Form	Form definition	Steel parts material	D1	D2	D3	D4	D6	D7	D8	H	H1	H2	L1	L2	L3	L4
06287-2100X06	D	pre-drilled	stainless steel 1.4305	100	6	22	20	79	M6	29	12	9	8	29,5	19	39	54,7
06287-2125X08	D	pre-drilled	stainless steel 1.4305	125	8	26	21	101	M6	34	15	9	8	34	24	46	54,7
06287-2140X08	D	pre-drilled	stainless steel 1.4305	140	8	30	25	110	M8	39	16	12	8	38,5	27	52	82,2
06287-2160X10	D	pre-drilled	stainless steel 1.4305	160	10	33	30	128	M8	43	20	12	8	41,3	30,1	57	82,2
06287-3100X10	E	with reamed hole	stainless steel 1.4305	100	10H7	22	20	79	M6	29	-	9	8	29,5	19	39	54,7
06287-3125X12	E	with reamed hole	stainless steel 1.4305	125	12H7	26	21	101	M6	34	-	9	8	34	24	46	54,7
06287-3140X14	E	with reamed hole	stainless steel 1.4305	140	14H7	30	25	110	M8	39	-	12	8	38,5	27	52	82,2
06287-3160X16	E	with reamed hole	stainless steel 1.4305	160	16H7	33	30	128	M8	43	-	12	8	41,3	30,1	57	82,2
06287-3160X18	E	with reamed hole	stainless steel 1.4305	160	18H7	33	30	128	M8	43	-	12	8	41,3	30,1	57	82,2