

Item description/product images

19"

**Description****Material:**

Tray and grip aluminium profile.

End caps polyamide.

Form A: Rubber profile for mounting.

Form B: 2 steel countersunk screws for mounting.

Version:

Tray and grip glass-bead blasted, satin finish and anodised black or natural colour.

Rubber profile black.

Fastening screws electro zinc-plated.

Note:

Form A handles can be mounted without screws for material thicknesses of 1 - 2.5 mm using 2 rubber profiles.

Form B handles can be mounted from the front with 2 countersunk screws.


Two cross-slots for M4 screws allow earthing connection and can serve as a mounting aid for additional parts.

Assembly:

After fitting the lower rubber profile, press the two side caps onto the handle. Next press the handle over the lower edge of the mounting cutout at a 45° angle and then push it up against the housing panel.

Now push the 2nd rubber profile into the upper groove or fix in place with 2 countersunk screws.

Drawings



Overview of items

Order No. black	Order No. natural	Form	Version 2	H	L	L1	T	Mounting cutout	Load capacity N
06961-10011	06961-10013	A	plug-in	90	100	115	19,5	107 x 73	500
06961-11811	06961-11813	A	plug-in	90	118	133	19,5	125 x 73	500
06961-16711	06961-16713	A	plug-in	90	167	182	19,5	174 x 73	500
06961-10021	06961-10023	B	screw on	90	100	115	19,5	107 x 73	500
06961-11821	06961-11823	B	screw on	90	118	133	19,5	125 x 73	500
06961-16721	06961-16723	B	screw on	90	167	182	19,5	174 x 73	500