



Item description/product images



Hinges with closing spring



Hinges with opening spring



Description

Material:

Aluminium 6060 T5.

End caps PA 6.6.

Washers POM.

Version:

Black anodised

Note:

The hinges are fitted with an integrated steel tension spring. This enables automatic opening and closing of doors and hatches.

Due to the same dimensions and appearance, the free-swinging hinges can be combined with the hinges with springs.

Opening angle 270°.

Opening spring torque:

$M(0^\circ) : 0.35 \text{ Nm} / M(90^\circ) : 0.24 \text{ Nm} / M(180^\circ) : 0.12 \text{ Nm}$

Closing spring torque:

$M(0^\circ) : 0.12 \text{ Nm} / M(90^\circ) : 0.24 \text{ Nm} / M(180^\circ) : 0.35 \text{ Nm}$

These hinges are designed for more than 30,000 switching cycles.

Fastened using DIN 912/DIN EN ISO 4762 cap screws.

The loading values given for the hinges are non-binding reference values, which do not consider safety factors and exclude any liability. The values given are for information purposes only and do not constitute a legally binding assurance of properties.

These load values were determined under laboratory conditions. Each user must determine individually whether the hinge is suitable for the respective application. Different materials onto which the hinges are installed and the type of mounting, weather conditions and wear can influence the determined values.


Temperature range:

From -20°C to +80°C

Accessory:

Socket head screws with hexagon socket DIN 912/EN ISO 4762.

Drawings



Overview of items

Order No.	Version 1	Version 2	Main colour	Surface finish body	A	A1	B	B1	D	D1	S	F1 N	F2 N
27906-556701	for mounting SWA39 base rail	-	9 hours	for handwheels	55	38	67	48	6,3	18	4,5	5000	4200
27906-55670	for mounting SWA39 base rail	-	Plug	for handwheels	55	38	67	48	6,3	18	4,5	5000	4200
27906-556711	for nc vice	-	9-pin	for handwheels	55	38	67	48	6,3	18	4,5	5000	4200
27906-55671	for nc vice	-	Plug	for handwheels	55	38	67	48	6,3	18	4,5	5000	4200
27906-055652	standard	-	Plug	for hex socket	55	38	65	48	6,3	18	4,5	6590	9810
27906-0556521	standard	-	above	for hex socket	55	38	65	48	6,3	18	4,5	6590	9810
27906-155652	standard	-	Plug	for hex socket	55	38	65	48	6,3	18	4,5	6590	9810
27906-1556521	standard	-	above	for hex socket	55	38	65	48	6,3	18	4,5	6590	9810