


Item description/product images



Description


Material:

Sleeve and spring stainless steel.
Ball stainless steel or POM.

Version:

Sleeve bright.
Steel ball hardened and bright.

Drawings



Overview of items

Order No.	Component material	D	D1	D2	L	L1	Travel S	Spring force initial pressure F1 approx. N	Spring force final pressure F2 approx. N
03070-02	25/grid 50	2	1,5	2,5	3	0,6	0,4	1,2	2,5
03070-03	22012-10161	3	2,5	3,5	4	0,8	0,65	1,7	3,4
03070-04	22012-10161	4	3	4,6	5	1	0,8	3	7
03070-05	22012-10161	5	4	5,6	6	1	1	4	7
03070-06	22012-10161	6	5	6,5	7	1	1,5	6	12

Overview of items

Order No.	Component material	D	D1	D2	L	L1	Travel S	Spring force initial pressure F1 approx. N	Spring force final pressure F2 approx. N
03070-08	22012-10161	8	6,5	8,5	9	1	1,8	6	12
03070-10	22012-10161	10	8	12	13,5	2,5	2,7	10	20
03070-12	22012-10161	12	10	14	16	2,5	3,5	15	25
03070-304	3-axis vice with 50 mm riser plate	4	3	4,6	5	1	0,6	3	7
03070-305	3-axis vice with 50 mm riser plate	5	4	5,6	6	1	0,8	4	7
03070-306	3-axis vice with 50 mm riser plate	6	5	6,5	7	1	1,3	6	12
03070-308	3-axis vice with 50 mm riser plate	8	6,5	8,5	9	1	1,6	6	12
03070-310	3-axis vice with 50 mm riser plate	10	8	12	13,5	2,5	2,6	10	20
03070-312	3-axis vice with 50 mm riser plate	12	10	14	16	2,5	3,3	15	25