## 28001 Oil level gauges long version

## norelem

#### tem description/product images



## Description

#### Material:

Housing aluminium. Tube polycarbonate. Caps polyamide. O-ring and flat seal NBR, Shore 70. Screw and hex. nut steel.

#### Version:

Viewing glass transparent. Screws and nuts electro zinc-plated.

#### Note:

The oil level gauges can either be fastened as shown in the illustration or directly in the tapped hole. Centre distance for the fastening holes =  $L1\pm0.3$ . The maximum operating temperature is 90 °C. The maximum pressure is 1 bar. The maximum tightening torque of the fastening screws is 5 Nm.

**Drawing reference:** 

- 1) flat seal
- 2) 0-ring

### Drawings



# Overview of items

Order No.	В	D1	Н	H1	L	L1
28001-1300	30	M12	30	16,5	325	300
28001-1400	30	M12	30	16,5	425	400
28001-1500	30	M12	30	16,5	525	500