tem description/product images





Description

Material:

Housing high-strength aluminium. Stop system steel.

Version:

Housing anodised. Stop system hardened and black oxidised.

Note:

Maintenance-free pneumatic rotary module for small installation spaces with double actuated drive cylinder. Control by 4/2 or 5/2 directional valve. Pneumatic drive, 4-8 bar, constant, filtered (10 μ m), dried, oiled or unoiled. Compressed air connection M5.

Modules of the same size can be combined with one another without adapter plates via the precise centring system by means of centring rings 20240.

The $0^{\circ} - 190^{\circ}$ rotation angle is infinitely adjustable.

Repeat accuracy ±0.01°.

Accessory:

See table for shock absorber, proximitiy switch and plug connector.



_____ with shock absorber ____ without shock absorber

swivel time (s)

Overview of items

ľ	20060-014	4	0,28	0° - 190°	300	220	2 x 10	5
				angle	N	N		6 bar (ccm)
	Order No.	Size	Driving torque Nm		Axial Ioad	Radial load	Cylinder	Air consumption per cycle at

1	20060-014	4	26300-1010008	83000-15-010	80100-10-010X2000
			absorber	switch	connector
			shock		plug
	Order No.	Size	Suitable	Suitable	Suitable