

Item description/product images



Description


Material:

Black grey thermoplastic.


Threaded pin steel 5.8 or stainless steel 1.4305.

Version:

Steel trivalent blue passivated, stainless steel bright.



Drawings



Overview of items

Order No.	Material	Colour Cap	D	D1	D2	D3	H	H1	L
06092-105X10	steel	black grey RAL 7021	M5	21	14	19	22	8	10
06092-1051X10	steel	orange RAL 2004	M5	21	14	19	22	8	10
06092-1052X10	steel	signal green RAL6032	M5	21	14	19	22	8	10
06092-1053X10	steel	blue RAL5017	M5	21	14	19	22	8	10
06092-1055X10	steel	light grey RAL 7035	M5	21	14	19	22	8	10
06092-1056X10	steel	traffic red RAL 3020	M5	21	14	19	22	8	10
06092-1057X10	steel	colza yellow RAL 1021	M5	21	14	19	22	8	10
06092-105X12	steel	black grey RAL 7021	M5	21	14	19	22	8	12
06092-1051X12	steel	orange RAL 2004	M5	21	14	19	22	8	12
06092-1052X12	steel	signal green RAL6032	M5	21	14	19	22	8	12
06092-1053X12	steel	blue RAL5017	M5	21	14	19	22	8	12
06092-1055X12	steel	light grey RAL 7035	M5	21	14	19	22	8	12
06092-1056X12	steel	traffic red RAL 3020	M5	21	14	19	22	8	12
06092-1057X12	steel	colza yellow RAL 1021	M5	21	14	19	22	8	12
06092-105X15	steel	black grey RAL 7021	M5	21	14	19	22	8	15
06092-1051X15	steel	orange RAL 2004	M5	21	14	19	22	8	15
06092-1052X15	steel	signal green RAL6032	M5	21	14	19	22	8	15
06092-1053X15	steel	blue RAL5017	M5	21	14	19	22	8	15
06092-1055X15	steel	light grey RAL 7035	M5	21	14	19	22	8	15
06092-1056X15	steel	traffic red RAL 3020	M5	21	14	19	22	8	15
06092-1057X15	steel	colza yellow RAL 1021	M5	21	14	19	22	8	15
06092-105X20	steel	black grey RAL 7021	M5	21	14	19	22	8	20
06092-1051X20	steel	orange RAL 2004	M5	21	14	19	22	8	20
06092-1052X20	steel	signal green RAL6032	M5	21	14	19	22	8	20
06092-1053X20	steel	blue RAL5017	M5	21	14	19	22	8	20
06092-1055X20	steel	light grey RAL 7035	M5	21	14	19	22	8	20
06092-1056X20	steel	traffic red RAL 3020	M5	21	14	19	22	8	20
06092-1057X20	steel	colza yellow RAL 1021	M5	21	14	19	22	8	20
06092-105X25	steel	black grey RAL 7021	M5	21	14	19	22	8	25
06092-1051X25	steel	orange RAL 2004	M5	21	14	19	22	8	25
06092-1052X25	steel	signal green RAL6032	M5	21	14	19	22	8	25
06092-1053X25	steel	blue RAL5017	M5	21	14	19	22	8	25
06092-1055X25	steel	light grey RAL 7035	M5	21	14	19	22	8	25
06092-1056X25	steel	traffic red RAL 3020	M5	21	14	19	22	8	25
06092-1057X25	steel	colza yellow RAL 1021	M5	21	14	19	22	8	25
06092-106X15	steel	black grey RAL 7021	M6	21	14	19	22	8	15
06092-1061X15	steel	orange RAL 2004	M6	21	14	19	22	8	15
06092-1062X15	steel	signal green RAL6032	M6	21	14	19	22	8	15
06092-1063X15	steel	blue RAL5017	M6	21	14	19	22	8	15
06092-1065X15	steel	light grey RAL 7035	M6	21	14	19	22	8	15
06092-1066X15	steel	traffic red RAL 3020	M6	21	14	19	22	8	15
06092-1067X15	steel	colza yellow RAL 1021	M6	21	14	19	22	8	15
06092-106X20	steel	black grey RAL 7021	M6	21	14	19	22	8	20
06092-1061X20	steel	orange RAL 2004	M6	21	14	19	22	8	20
06092-1062X20	steel	signal green RAL6032	M6	21	14	19	22	8	20
06092-1063X20	steel	blue RAL5017	M6	21	14	19	22	8	20
06092-1065X20	steel	light grey RAL 7035	M6	21	14	19	22	8	20
06092-1066X20	steel	traffic red RAL 3020	M6	21	14	19	22	8	20
06092-1067X20	steel	colza yellow RAL 1021	M6	21	14	19	22	8	20
06092-106X25	steel	black grey RAL 7021	M6	21	14	19	22	8	25
06092-1061X25	steel	orange RAL 2004	M6	21	14	19	22	8	25
06092-1062X25	steel	signal green RAL6032	M6	21	14	19	22	8	25
06092-1063X25	steel	blue RAL5017	M6	21	14	19	22	8	25
06092-1065X25	steel	light grey RAL 7035	M6	21	14	19	22	8	25
06092-1066X25	steel	traffic red RAL 3020	M6	21	14	19	22	8	25
06092-1067X25	steel	colza yellow RAL 1021	M6	21	14	19	22	8	25
06092-106X30	steel	black grey RAL 7021	M6	21	14	19	22	8	30
06092-1061X30	steel	orange RAL 2004	M6	21	14	19	22	8	30
06092-1062X30	steel	signal green RAL6032	M6	21	14	19	22	8	30
06092-1063X30	steel	blue RAL5017	M6	21	14	19	22	8	30
06092-1065X30	steel	light grey RAL 7035	M6	21	14	19	22	8	30
06092-1066X30	steel	traffic red RAL 3020	M6	21	14	19	22	8	30
06092-1067X30	steel	colza yellow RAL 1021	M6	21	14	19	22	8	30
06092-208X20	steel	black grey RAL 7021	M8	26	18	23	26	9,5	20
06092-2081X20	steel	orange RAL 2004	M8	26	18	23	26	9,5	20

Overview of items

Order No.	Material	Colour Cap	D	D1	D2	D3	H	H1	L
06092-2082X20	steel	signal green RAL6032	M8	26	18	23	26	9,5	20
06092-2083X20	steel	blue RAL5017	M8	26	18	23	26	9,5	20
06092-2085X20	steel	light grey RAL 7035	M8	26	18	23	26	9,5	20
06092-2086X20	steel	traffic red RAL 3020	M8	26	18	23	26	9,5	20
06092-2087X20	steel	colza yellow RAL 1021	M8	26	18	23	26	9,5	20
06092-208X25	steel	black grey RAL 7021	M8	26	18	23	26	9,5	25
06092-2081X25	steel	orange RAL 2004	M8	26	18	23	26	9,5	25
06092-2082X25	steel	signal green RAL6032	M8	26	18	23	26	9,5	25
06092-2083X25	steel	blue RAL5017	M8	26	18	23	26	9,5	25
06092-2085X25	steel	light grey RAL 7035	M8	26	18	23	26	9,5	25
06092-2086X25	steel	traffic red RAL 3020	M8	26	18	23	26	9,5	25
06092-2087X25	steel	colza yellow RAL 1021	M8	26	18	23	26	9,5	25
06092-208X30	steel	black grey RAL 7021	M8	26	18	23	26	9,5	30
06092-2081X30	steel	orange RAL 2004	M8	26	18	23	26	9,5	30
06092-2082X30	steel	signal green RAL6032	M8	26	18	23	26	9,5	30
06092-2083X30	steel	blue RAL5017	M8	26	18	23	26	9,5	30
06092-2085X30	steel	light grey RAL 7035	M8	26	18	23	26	9,5	30
06092-2086X30	steel	traffic red RAL 3020	M8	26	18	23	26	9,5	30
06092-2087X30	steel	colza yellow RAL 1021	M8	26	18	23	26	9,5	30
06092-208X40	steel	black grey RAL 7021	M8	26	18	23	26	9,5	40
06092-2081X40	steel	orange RAL 2004	M8	26	18	23	26	9,5	40
06092-2082X40	steel	signal green RAL6032	M8	26	18	23	26	9,5	40
06092-2083X40	steel	blue RAL5017	M8	26	18	23	26	9,5	40
06092-2085X40	steel	light grey RAL 7035	M8	26	18	23	26	9,5	40
06092-2086X40	steel	traffic red RAL 3020	M8	26	18	23	26	9,5	40
06092-2087X40	steel	colza yellow RAL 1021	M8	26	18	23	26	9,5	40
06092-310X20	steel	black grey RAL 7021	M10	34	22	31	36	13	20
06092-3101X20	steel	orange RAL 2004	M10	34	22	31	36	13	20
06092-3102X20	steel	signal green RAL6032	M10	34	22	31	36	13	20
06092-3103X20	steel	blue RAL5017	M10	34	22	31	36	13	20
06092-3105X20	steel	light grey RAL 7035	M10	34	22	31	36	13	20
06092-3106X20	steel	traffic red RAL 3020	M10	34	22	31	36	13	20
06092-3107X20	steel	colza yellow RAL 1021	M10	34	22	31	36	13	20
06092-310X30	steel	black grey RAL 7021	M10	34	22	31	36	13	30
06092-3101X30	steel	orange RAL 2004	M10	34	22	31	36	13	30
06092-3102X30	steel	signal green RAL6032	M10	34	22	31	36	13	30
06092-3103X30	steel	blue RAL5017	M10	34	22	31	36	13	30
06092-3105X30	steel	light grey RAL 7035	M10	34	22	31	36	13	30
06092-3106X30	steel	traffic red RAL 3020	M10	34	22	31	36	13	30
06092-3107X30	steel	colza yellow RAL 1021	M10	34	22	31	36	13	30
06092-310X40	steel	black grey RAL 7021	M10	34	22	31	36	13	40
06092-3101X40	steel	orange RAL 2004	M10	34	22	31	36	13	40
06092-3102X40	steel	signal green RAL6032	M10	34	22	31	36	13	40
06092-3103X40	steel	blue RAL5017	M10	34	22	31	36	13	40
06092-3105X40	steel	light grey RAL 7035	M10	34	22	31	36	13	40
06092-3106X40	steel	traffic red RAL 3020	M10	34	22	31	36	13	40
06092-3107X40	steel	colza yellow RAL 1021	M10	34	22	31	36	13	40
06092-0105X10	stainless steel	black grey RAL 7021	M5	21	14	19	22	8	10
06092-01051X10	stainless steel	orange RAL 2004	M5	21	14	19	22	8	10
06092-01052X10	stainless steel	signal green RAL6032	M5	21	14	19	22	8	10
06092-01053X10	stainless steel	blue RAL5017	M5	21	14	19	22	8	10
06092-01055X10	stainless steel	light grey RAL 7035	M5	21	14	19	22	8	10
06092-01056X10	stainless steel	traffic red RAL 3020	M5	21	14	19	22	8	10
06092-01057X10	stainless steel	colza yellow RAL 1021	M5	21	14	19	22	8	10
06092-0105X12	stainless steel	black grey RAL 7021	M5	21	14	19	22	8	12
06092-01051X12	stainless steel	orange RAL 2004	M5	21	14	19	22	8	12
06092-01052X12	stainless steel	signal green RAL6032	M5	21	14	19	22	8	12
06092-01053X12	stainless steel	blue RAL5017	M5	21	14	19	22	8	12
06092-01055X12	stainless steel	light grey RAL 7035	M5	21	14	19	22	8	12
06092-01056X12	stainless steel	traffic red RAL 3020	M5	21	14	19	22	8	12
06092-01057X12	stainless steel	colza yellow RAL 1021	M5	21	14	19	22	8	12
06092-0105X15	stainless steel	black grey RAL 7021	M5	21	14	19	22	8	15
06092-01051X15	stainless steel	orange RAL 2004	M5	21	14	19	22	8	15
06092-01052X15	stainless steel	signal green RAL6032	M5	21	14	19	22	8	15
06092-01053X15	stainless steel	blue RAL5017	M5	21	14	19	22	8	15

Overview of items

Order No.	Material	Colour Cap	D	D1	D2	D3	H	H1	L
06092-01055X15	stainless steel	light grey RAL 7035	M5	21	14	19	22	8	15
06092-01056X15	stainless steel	traffic red RAL 3020	M5	21	14	19	22	8	15
06092-01057X15	stainless steel	colza yellow RAL 1021	M5	21	14	19	22	8	15
06092-0105X20	stainless steel	black grey RAL 7021	M5	21	14	19	22	8	20
06092-01051X20	stainless steel	orange RAL 2004	M5	21	14	19	22	8	20
06092-01052X20	stainless steel	signal green RAL6032	M5	21	14	19	22	8	20
06092-01053X20	stainless steel	blue RAL5017	M5	21	14	19	22	8	20
06092-01055X20	stainless steel	light grey RAL 7035	M5	21	14	19	22	8	20
06092-01056X20	stainless steel	traffic red RAL 3020	M5	21	14	19	22	8	20
06092-01057X20	stainless steel	colza yellow RAL 1021	M5	21	14	19	22	8	20
06092-0105X25	stainless steel	black grey RAL 7021	M5	21	14	19	22	8	25
06092-01051X25	stainless steel	orange RAL 2004	M5	21	14	19	22	8	25
06092-01052X25	stainless steel	signal green RAL6032	M5	21	14	19	22	8	25
06092-01053X25	stainless steel	blue RAL5017	M5	21	14	19	22	8	25
06092-01055X25	stainless steel	light grey RAL 7035	M5	21	14	19	22	8	25
06092-01056X25	stainless steel	traffic red RAL 3020	M5	21	14	19	22	8	25
06092-01057X25	stainless steel	colza yellow RAL 1021	M5	21	14	19	22	8	25
06092-0106X15	stainless steel	black grey RAL 7021	M6	21	14	19	22	8	15
06092-01061X15	stainless steel	orange RAL 2004	M6	21	14	19	22	8	15
06092-01062X15	stainless steel	signal green RAL6032	M6	21	14	19	22	8	15
06092-01063X15	stainless steel	blue RAL5017	M6	21	14	19	22	8	15
06092-01065X15	stainless steel	light grey RAL 7035	M6	21	14	19	22	8	15
06092-01066X15	stainless steel	traffic red RAL 3020	M6	21	14	19	22	8	15
06092-01067X15	stainless steel	colza yellow RAL 1021	M6	21	14	19	22	8	15
06092-0106X20	stainless steel	black grey RAL 7021	M6	21	14	19	22	8	20
06092-01061X20	stainless steel	orange RAL 2004	M6	21	14	19	22	8	20
06092-01062X20	stainless steel	signal green RAL6032	M6	21	14	19	22	8	20
06092-01063X20	stainless steel	blue RAL5017	M6	21	14	19	22	8	20
06092-01065X20	stainless steel	light grey RAL 7035	M6	21	14	19	22	8	20
06092-01066X20	stainless steel	traffic red RAL 3020	M6	21	14	19	22	8	20
06092-01067X20	stainless steel	colza yellow RAL 1021	M6	21	14	19	22	8	20
06092-0106X25	stainless steel	black grey RAL 7021	M6	21	14	19	22	8	25
06092-01061X25	stainless steel	orange RAL 2004	M6	21	14	19	22	8	25
06092-01062X25	stainless steel	signal green RAL6032	M6	21	14	19	22	8	25
06092-01063X25	stainless steel	blue RAL5017	M6	21	14	19	22	8	25
06092-01065X25	stainless steel	light grey RAL 7035	M6	21	14	19	22	8	25
06092-01066X25	stainless steel	traffic red RAL 3020	M6	21	14	19	22	8	25
06092-01067X25	stainless steel	colza yellow RAL 1021	M6	21	14	19	22	8	25
06092-0106X30	stainless steel	black grey RAL 7021	M6	21	14	19	22	8	30
06092-01061X30	stainless steel	orange RAL 2004	M6	21	14	19	22	8	30
06092-01062X30	stainless steel	signal green RAL6032	M6	21	14	19	22	8	30
06092-01063X30	stainless steel	blue RAL5017	M6	21	14	19	22	8	30
06092-01065X30	stainless steel	light grey RAL 7035	M6	21	14	19	22	8	30
06092-01066X30	stainless steel	traffic red RAL 3020	M6	21	14	19	22	8	30
06092-01067X30	stainless steel	colza yellow RAL 1021	M6	21	14	19	22	8	30
06092-0208X20	stainless steel	black grey RAL 7021	M8	26	18	23	26	9,5	20
06092-02081X20	stainless steel	orange RAL 2004	M8	26	18	23	26	9,5	20
06092-02082X20	stainless steel	signal green RAL6032	M8	26	18	23	26	9,5	20
06092-02083X20	stainless steel	blue RAL5017	M8	26	18	23	26	9,5	20
06092-02085X20	stainless steel	light grey RAL 7035	M8	26	18	23	26	9,5	20
06092-02086X20	stainless steel	traffic red RAL 3020	M8	26	18	23	26	9,5	20
06092-02087X20	stainless steel	colza yellow RAL 1021	M8	26	18	23	26	9,5	20
06092-0208X25	stainless steel	black grey RAL 7021	M8	26	18	23	26	9,5	25
06092-02081X25	stainless steel	orange RAL 2004	M8	26	18	23	26	9,5	25
06092-02082X25	stainless steel	signal green RAL6032	M8	26	18	23	26	9,5	25
06092-02083X25	stainless steel	blue RAL5017	M8	26	18	23	26	9,5	25
06092-02085X25	stainless steel	light grey RAL 7035	M8	26	18	23	26	9,5	25
06092-02086X25	stainless steel	traffic red RAL 3020	M8	26	18	23	26	9,5	25
06092-02087X25	stainless steel	colza yellow RAL 1021	M8	26	18	23	26	9,5	25
06092-0208X30	stainless steel	black grey RAL 7021	M8	26	18	23	26	9,5	30
06092-02081X30	stainless steel	orange RAL 2004	M8	26	18	23	26	9,5	30
06092-02082X30	stainless steel	signal green RAL6032	M8	26	18	23	26	9,5	30
06092-02083X30	stainless steel	blue RAL5017	M8	26	18	23	26	9,5	30
06092-02085X30	stainless steel	light grey RAL 7035	M8	26	18	23	26	9,5	30
06092-02086X30	stainless steel	traffic red RAL 3020	M8	26	18	23	26	9,5	30

Overview of items

Order No.	Material	Colour Cap	D	D1	D2	D3	H	H1	L
06092-02087X30	stainless steel	colza yellow RAL 1021	M8	26	18	23	26	9,5	30
06092-0208X40	stainless steel	black grey RAL 7021	M8	26	18	23	26	9,5	40
06092-02081X40	stainless steel	orange RAL 2004	M8	26	18	23	26	9,5	40
06092-02082X40	stainless steel	signal green RAL6032	M8	26	18	23	26	9,5	40
06092-02083X40	stainless steel	blue RAL5017	M8	26	18	23	26	9,5	40
06092-02085X40	stainless steel	light grey RAL 7035	M8	26	18	23	26	9,5	40
06092-02086X40	stainless steel	traffic red RAL 3020	M8	26	18	23	26	9,5	40
06092-02087X40	stainless steel	colza yellow RAL 1021	M8	26	18	23	26	9,5	40
06092-0310X20	stainless steel	black grey RAL 7021	M10	34	22	31	36	13	20
06092-03101X20	stainless steel	orange RAL 2004	M10	34	22	31	36	13	20
06092-03102X20	stainless steel	signal green RAL6032	M10	34	22	31	36	13	20
06092-03103X20	stainless steel	blue RAL5017	M10	34	22	31	36	13	20
06092-03105X20	stainless steel	light grey RAL 7035	M10	34	22	31	36	13	20
06092-03106X20	stainless steel	traffic red RAL 3020	M10	34	22	31	36	13	20
06092-03107X20	stainless steel	colza yellow RAL 1021	M10	34	22	31	36	13	20
06092-0310X30	stainless steel	black grey RAL 7021	M10	34	22	31	36	13	30
06092-03101X30	stainless steel	orange RAL 2004	M10	34	22	31	36	13	30
06092-03102X30	stainless steel	signal green RAL6032	M10	34	22	31	36	13	30
06092-03103X30	stainless steel	blue RAL5017	M10	34	22	31	36	13	30
06092-03105X30	stainless steel	light grey RAL 7035	M10	34	22	31	36	13	30
06092-03106X30	stainless steel	traffic red RAL 3020	M10	34	22	31	36	13	30
06092-03107X30	stainless steel	colza yellow RAL 1021	M10	34	22	31	36	13	30
06092-0310X40	stainless steel	black grey RAL 7021	M10	34	22	31	36	13	40
06092-03101X40	stainless steel	orange RAL 2004	M10	34	22	31	36	13	40
06092-03102X40	stainless steel	signal green RAL6032	M10	34	22	31	36	13	40
06092-03103X40	stainless steel	blue RAL5017	M10	34	22	31	36	13	40
06092-03105X40	stainless steel	light grey RAL 7035	M10	34	22	31	36	13	40
06092-03106X40	stainless steel	traffic red RAL 3020	M10	34	22	31	36	13	40
06092-03107X40	stainless steel	colza yellow RAL 1021	M10	34	22	31	36	13	40