Item description/product images



Description

Material:
Black thermoplastic.
Bush and screw grade 5.8 steel.

Version:
Steel trivalent blue-passivated.

Drawing reference:
Form D: tapped bush without cap
Form K: tapped bush with cap
Form E: reamed bush without cap
Form H: reamed bush with cap
Form L: external thread

Drawings

Ⓓ Ⓚ



Ⓔ Ⓗ



Ⓛ





Overview of items

Order No.	Form	Colour Cap	Size	D	D1	D2	H	H1	T	L
06266-1105	D	-	1	M5	40	16,5	30	13	10	-
06266-1106	D	-	1	M6	40	16,5	30	13	10	-
06266-1108	D	-	1	M8	40	16,5	30	13	14	-
06266-1208	D	-	2	M8	50	18	35	15	14	-
06266-1210	D	-	2	M10	50	18	35	15	14	-
06266-1310	D	-	3	M10	63	22	40	17	14	-
06266-1312	D	-	3	M12	63	22	40	17	18	-
06266-2105	K	black grey RAL 7021	1	M5	40	16,5	31	13	10	-
06266-21051	K	orange RAL 2004	1	M5	40	16,5	31	13	10	-
06266-21052	K	signal green RAL6032	1	M5	40	16,5	31	13	10	-
06266-21053	K	blue RAL5017	1	M5	40	16,5	31	13	10	-
06266-21055	K	light grey RAL 7035	1	M5	40	16,5	31	13	10	-
06266-21056	K	traffic red RAL 3020	1	M5	40	16,5	31	13	10	-
06266-21057	K	colza yellow RAL 1021	1	M5	40	16,5	31	13	10	-
06266-2106	K	black grey RAL 7021	1	M6	40	16,5	31	13	10	-
06266-21061	K	orange RAL 2004	1	M6	40	16,5	31	13	10	-
06266-21062	K	signal green RAL6032	1	M6	40	16,5	31	13	10	-
06266-21063	K	blue RAL5017	1	M6	40	16,5	31	13	10	-
06266-21065	K	light grey RAL 7035	1	M6	40	16,5	31	13	10	-
06266-21066	K	traffic red RAL 3020	1	M6	40	16,5	31	13	10	-
06266-21067	K	colza yellow RAL 1021	1	M6	40	16,5	31	13	10	-
06266-2108	K	black grey RAL 7021	1	M8	40	16,5	31	13	14	-
06266-21081	K	orange RAL 2004	1	M8	40	16,5	31	13	14	-
06266-21082	K	signal green RAL6032	1	M8	40	16,5	31	13	14	-
06266-21083	K	blue RAL5017	1	M8	40	16,5	31	13	14	-
06266-21085	K	light grey RAL 7035	1	M8	40	16,5	31	13	14	-
06266-21086	K	traffic red RAL 3020	1	M8	40	16,5	31	13	14	-
06266-21087	K	colza yellow RAL 1021	1	M8	40	16,5	31	13	14	-
06266-2208	K	black grey RAL 7021	2	M8	50	18	36	15	14	-
06266-22081	K	orange RAL 2004	2	M8	50	18	36	15	14	-
06266-22082	K	signal green RAL6032	2	M8	50	18	36	15	14	-
06266-22083	K	blue RAL5017	2	M8	50	18	36	15	14	-
06266-22085	K	light grey RAL 7035	2	M8	50	18	36	15	14	-
06266-22086	K	traffic red RAL 3020	2	M8	50	18	36	15	14	-
06266-22087	K	colza yellow RAL 1021	2	M8	50	18	36	15	14	-
06266-2210	K	black grey RAL 7021	2	M10	50	18	36	15	14	-
06266-22101	K	orange RAL 2004	2	M10	50	18	36	15	14	-
06266-22102	K	signal green RAL6032	2	M10	50	18	36	15	14	-
06266-22103	K	blue RAL5017	2	M10	50	18	36	15	14	-
06266-22105	K	light grey RAL 7035	2	M10	50	18	36	15	14	-
06266-22106	K	traffic red RAL 3020	2	M10	50	18	36	15	14	-
06266-22107	K	colza yellow RAL 1021	2	M10	50	18	36	15	14	-
06266-2310	K	black grey RAL 7021	3	M10	63	22	41	17	14	-
06266-23101	K	orange RAL 2004	3	M10	63	22	41	17	14	-
06266-23102	K	signal green RAL6032	3	M10	63	22	41	17	14	-
06266-23103	K	blue RAL5017	3	M10	63	22	41	17	14	-
06266-23105	K	light grey RAL 7035	3	M10	63	22	41	17	14	-
06266-23106	K	traffic red RAL 3020	3	M10	63	22	41	17	14	-
06266-23107	K	colza yellow RAL 1021	3	M10	63	22	41	17	14	-
06266-2312	K	black grey RAL 7021	3	M12	63	22	41	17	18	-
06266-23121	K	orange RAL 2004	3	M12	63	22	41	17	18	-
06266-23122	K	signal green RAL6032	3	M12	63	22	41	17	18	-
06266-23123	K	blue RAL5017	3	M12	63	22	41	17	18	-
06266-23125	K	light grey RAL 7035	3	M12	63	22	41	17	18	-
06266-23126	K	traffic red RAL 3020	3	M12	63	22	41	17	18	-
06266-23127	K	colza yellow RAL 1021	3	M12	63	22	41	17	18	-
06266-3106	E	-	1	6	40	16,5	30	13	10	-
06266-3208	E	-	2	8	50	18	35	15	14	-
06266-3310	E	-	3	10	63	22	40	17	14	-
06266-4106	H	black grey RAL 7021	1	6	40	16,5	31	13	10	-
06266-41061	H	orange RAL 2004	1	6	40	16,5	31	13	10	-
06266-41062	H	signal green RAL6032	1	6	40	16,5	31	13	10	-
06266-41063	H	blue RAL5017	1	6	40	16,5	31	13	10	-
06266-41065	H	light grey RAL 7035	1	6	40	16,5	31	13	10	-
06266-41066	H	traffic red RAL 3020	1	6	40	16,5	31	13	10	-

Overview of items

Order No.	Form	Colour Cap	Size	D	D1	D2	H	H1	T	L
06266-41067	H	colza yellow RAL 1021	1	6	40	16,5	31	13	10	-
06266-4208	H	black grey RAL 7021	2	8	50	18	36	15	14	-
06266-42081	H	orange RAL 2004	2	8	50	18	36	15	14	-
06266-42082	H	signal green RAL6032	2	8	50	18	36	15	14	-
06266-42083	H	blue RAL5017	2	8	50	18	36	15	14	-
06266-42085	H	light grey RAL 7035	2	8	50	18	36	15	14	-
06266-42086	H	traffic red RAL 3020	2	8	50	18	36	15	14	-
06266-42087	H	colza yellow RAL 1021	2	8	50	18	36	15	14	-
06266-4310	H	black grey RAL 7021	3	10	63	22	41	17	14	-
06266-43101	H	orange RAL 2004	3	10	63	22	41	17	14	-
06266-43102	H	signal green RAL6032	3	10	63	22	41	17	14	-
06266-43103	H	blue RAL5017	3	10	63	22	41	17	14	-
06266-43105	H	light grey RAL 7035	3	10	63	22	41	17	14	-
06266-43106	H	traffic red RAL 3020	3	10	63	22	41	17	14	-
06266-43107	H	colza yellow RAL 1021	3	10	63	22	41	17	14	-
06266-5105X10	L	black grey RAL 7021	1	M5	40	16,5	31	13	-	10
06266-51051X10	L	orange RAL 2004	1	M5	40	16,5	31	13	-	10
06266-51052X10	L	signal green RAL6032	1	M5	40	16,5	31	13	-	10
06266-51053X10	L	blue RAL5017	1	M5	40	16,5	31	13	-	10
06266-51055X10	L	light grey RAL 7035	1	M5	40	16,5	31	13	-	10
06266-51056X10	L	traffic red RAL 3020	1	M5	40	16,5	31	13	-	10
06266-51057X10	L	colza yellow RAL 1021	1	M5	40	16,5	31	13	-	10
06266-5105X20	L	black grey RAL 7021	1	M5	40	16,5	31	13	-	20
06266-51051X20	L	orange RAL 2004	1	M5	40	16,5	31	13	-	20
06266-51052X20	L	signal green RAL6032	1	M5	40	16,5	31	13	-	20
06266-51053X20	L	blue RAL5017	1	M5	40	16,5	31	13	-	20
06266-51055X20	L	light grey RAL 7035	1	M5	40	16,5	31	13	-	20
06266-51056X20	L	traffic red RAL 3020	1	M5	40	16,5	31	13	-	20
06266-51057X20	L	colza yellow RAL 1021	1	M5	40	16,5	31	13	-	20
06266-5105X40	L	black grey RAL 7021	1	M5	40	16,5	31	13	-	40
06266-51051X40	L	orange RAL 2004	1	M5	40	16,5	31	13	-	40
06266-51052X40	L	signal green RAL6032	1	M5	40	16,5	31	13	-	40
06266-51053X40	L	blue RAL5017	1	M5	40	16,5	31	13	-	40
06266-51055X40	L	light grey RAL 7035	1	M5	40	16,5	31	13	-	40
06266-51056X40	L	traffic red RAL 3020	1	M5	40	16,5	31	13	-	40
06266-51057X40	L	colza yellow RAL 1021	1	M5	40	16,5	31	13	-	40
06266-5106X10	L	black grey RAL 7021	1	M6	40	16,5	31	13	-	10
06266-51061X10	L	orange RAL 2004	1	M6	40	16,5	31	13	-	10
06266-51062X10	L	signal green RAL6032	1	M6	40	16,5	31	13	-	10
06266-51063X10	L	blue RAL5017	1	M6	40	16,5	31	13	-	10
06266-51065X10	L	light grey RAL 7035	1	M6	40	16,5	31	13	-	10
06266-51066X10	L	traffic red RAL 3020	1	M6	40	16,5	31	13	-	10
06266-51067X10	L	colza yellow RAL 1021	1	M6	40	16,5	31	13	-	10
06266-5106X20	L	black grey RAL 7021	1	M6	40	16,5	31	13	-	20
06266-51061X20	L	orange RAL 2004	1	M6	40	16,5	31	13	-	20
06266-51062X20	L	signal green RAL6032	1	M6	40	16,5	31	13	-	20
06266-51063X20	L	blue RAL5017	1	M6	40	16,5	31	13	-	20
06266-51065X20	L	light grey RAL 7035	1	M6	40	16,5	31	13	-	20
06266-51066X20	L	traffic red RAL 3020	1	M6	40	16,5	31	13	-	20
06266-51067X20	L	colza yellow RAL 1021	1	M6	40	16,5	31	13	-	20
06266-5106X40	L	black grey RAL 7021	1	M6	40	16,5	31	13	-	40
06266-51061X40	L	orange RAL 2004	1	M6	40	16,5	31	13	-	40
06266-51062X40	L	signal green RAL6032	1	M6	40	16,5	31	13	-	40
06266-51063X40	L	blue RAL5017	1	M6	40	16,5	31	13	-	40
06266-51065X40	L	light grey RAL 7035	1	M6	40	16,5	31	13	-	40
06266-51066X40	L	traffic red RAL 3020	1	M6	40	16,5	31	13	-	40
06266-51067X40	L	colza yellow RAL 1021	1	M6	40	16,5	31	13	-	40
06266-5108X15	L	black grey RAL 7021	1	M8	40	16,5	31	13	-	15
06266-51081X15	L	orange RAL 2004	1	M8	40	16,5	31	13	-	15
06266-51082X15	L	signal green RAL6032	1	M8	40	16,5	31	13	-	15
06266-51083X15	L	blue RAL5017	1	M8	40	16,5	31	13	-	15
06266-51085X15	L	light grey RAL 7035	1	M8	40	16,5	31	13	-	15
06266-51086X15	L	traffic red RAL 3020	1	M8	40	16,5	31	13	-	15
06266-51087X15	L	colza yellow RAL 1021	1	M8	40	16,5	31	13	-	15
06266-5108X30	L	black grey RAL 7021	1	M8	40	16,5	31	13	-	30

Overview of items

Order No.	Form	Colour Cap	Size	D	D1	D2	H	H1	T	L
06266-51081X30	L	orange RAL 2004	1	M8	40	16,5	31	13	-	30
06266-51082X30	L	signal green RAL6032	1	M8	40	16,5	31	13	-	30
06266-51083X30	L	blue RAL5017	1	M8	40	16,5	31	13	-	30
06266-51085X30	L	light grey RAL 7035	1	M8	40	16,5	31	13	-	30
06266-51086X30	L	traffic red RAL 3020	1	M8	40	16,5	31	13	-	30
06266-51087X30	L	colza yellow RAL 1021	1	M8	40	16,5	31	13	-	30
06266-5108X60	L	black grey RAL 7021	1	M8	40	16,5	31	13	-	60
06266-51081X60	L	orange RAL 2004	1	M8	40	16,5	31	13	-	60
06266-51082X60	L	signal green RAL6032	1	M8	40	16,5	31	13	-	60
06266-51083X60	L	blue RAL5017	1	M8	40	16,5	31	13	-	60
06266-51085X60	L	light grey RAL 7035	1	M8	40	16,5	31	13	-	60
06266-51086X60	L	traffic red RAL 3020	1	M8	40	16,5	31	13	-	60
06266-51087X60	L	colza yellow RAL 1021	1	M8	40	16,5	31	13	-	60
06266-5208X15	L	black grey RAL 7021	2	M8	50	18	36	15	-	15
06266-52081X15	L	orange RAL 2004	2	M8	50	18	36	15	-	15
06266-52082X15	L	signal green RAL6032	2	M8	50	18	36	15	-	15
06266-52083X15	L	blue RAL5017	2	M8	50	18	36	15	-	15
06266-52085X15	L	light grey RAL 7035	2	M8	50	18	36	15	-	15
06266-52086X15	L	traffic red RAL 3020	2	M8	50	18	36	15	-	15
06266-52087X15	L	colza yellow RAL 1021	2	M8	50	18	36	15	-	15
06266-5208X30	L	black grey RAL 7021	2	M8	50	18	36	15	-	30
06266-52081X30	L	orange RAL 2004	2	M8	50	18	36	15	-	30
06266-52082X30	L	signal green RAL6032	2	M8	50	18	36	15	-	30
06266-52083X30	L	blue RAL5017	2	M8	50	18	36	15	-	30
06266-52085X30	L	light grey RAL 7035	2	M8	50	18	36	15	-	30
06266-52086X30	L	traffic red RAL 3020	2	M8	50	18	36	15	-	30
06266-52087X30	L	colza yellow RAL 1021	2	M8	50	18	36	15	-	30
06266-5208X60	L	black grey RAL 7021	2	M8	50	18	36	15	-	60
06266-52081X60	L	orange RAL 2004	2	M8	50	18	36	15	-	60
06266-52082X60	L	signal green RAL6032	2	M8	50	18	36	15	-	60
06266-52083X60	L	blue RAL5017	2	M8	50	18	36	15	-	60
06266-52085X60	L	light grey RAL 7035	2	M8	50	18	36	15	-	60
06266-52086X60	L	traffic red RAL 3020	2	M8	50	18	36	15	-	60
06266-52087X60	L	colza yellow RAL 1021	2	M8	50	18	36	15	-	60
06266-5210X20	L	black grey RAL 7021	2	M10	50	18	36	15	-	20
06266-52101X20	L	orange RAL 2004	2	M10	50	18	36	15	-	20
06266-52102X20	L	signal green RAL6032	2	M10	50	18	36	15	-	20
06266-52103X20	L	blue RAL5017	2	M10	50	18	36	15	-	20
06266-52105X20	L	light grey RAL 7035	2	M10	50	18	36	15	-	20
06266-52106X20	L	traffic red RAL 3020	2	M10	50	18	36	15	-	20
06266-52107X20	L	colza yellow RAL 1021	2	M10	50	18	36	15	-	20
06266-5210X30	L	black grey RAL 7021	2	M10	50	18	36	15	-	30
06266-52101X30	L	orange RAL 2004	2	M10	50	18	36	15	-	30
06266-52102X30	L	signal green RAL6032	2	M10	50	18	36	15	-	30
06266-52103X30	L	blue RAL5017	2	M10	50	18	36	15	-	30
06266-52105X30	L	light grey RAL 7035	2	M10	50	18	36	15	-	30
06266-52106X30	L	traffic red RAL 3020	2	M10	50	18	36	15	-	30
06266-52107X30	L	colza yellow RAL 1021	2	M10	50	18	36	15	-	30
06266-5210X60	L	black grey RAL 7021	2	M10	50	18	36	15	-	60
06266-52101X60	L	orange RAL 2004	2	M10	50	18	36	15	-	60
06266-52102X60	L	signal green RAL6032	2	M10	50	18	36	15	-	60
06266-52103X60	L	blue RAL5017	2	M10	50	18	36	15	-	60
06266-52105X60	L	light grey RAL 7035	2	M10	50	18	36	15	-	60
06266-52106X60	L	traffic red RAL 3020	2	M10	50	18	36	15	-	60
06266-52107X60	L	colza yellow RAL 1021	2	M10	50	18	36	15	-	60
06266-5310X20	L	black grey RAL 7021	3	M10	63	22	41	17	-	20
06266-53101X20	L	orange RAL 2004	3	M10	63	22	41	17	-	20
06266-53102X20	L	signal green RAL6032	3	M10	63	22	41	17	-	20
06266-53103X20	L	blue RAL5017	3	M10	63	22	41	17	-	20
06266-53105X20	L	light grey RAL 7035	3	M10	63	22	41	17	-	20
06266-53106X20	L	traffic red RAL 3020	3	M10	63	22	41	17	-	20
06266-53107X20	L	colza yellow RAL 1021	3	M10	63	22	41	17	-	20
06266-5310X30	L	black grey RAL 7021	3	M10	63	22	41	17	-	30
06266-53101X30	L	orange RAL 2004	3	M10	63	22	41	17	-	30
06266-53102X30	L	signal green RAL6032	3	M10	63	22	41	17	-	30

Overview of items

Order No.	Form	Colour Cap	Size	D	D1	D2	H	H1	T	L
06266-53103X30	L	blue RAL5017	3	M10	63	22	41	17	-	30
06266-53105X30	L	light grey RAL 7035	3	M10	63	22	41	17	-	30
06266-53106X30	L	traffic red RAL 3020	3	M10	63	22	41	17	-	30
06266-53107X30	L	colza yellow RAL 1021	3	M10	63	22	41	17	-	30
06266-5310X60	L	black grey RAL 7021	3	M10	63	22	41	17	-	60
06266-53101X60	L	orange RAL 2004	3	M10	63	22	41	17	-	60
06266-53102X60	L	signal green RAL6032	3	M10	63	22	41	17	-	60
06266-53103X60	L	blue RAL5017	3	M10	63	22	41	17	-	60
06266-53105X60	L	light grey RAL 7035	3	M10	63	22	41	17	-	60
06266-53106X60	L	traffic red RAL 3020	3	M10	63	22	41	17	-	60
06266-53107X60	L	colza yellow RAL 1021	3	M10	63	22	41	17	-	60
06266-5312X30	L	black grey RAL 7021	3	M12	63	22	41	17	-	30
06266-53121X30	L	orange RAL 2004	3	M12	63	22	41	17	-	30
06266-53122X30	L	signal green RAL6032	3	M12	63	22	41	17	-	30
06266-53123X30	L	blue RAL5017	3	M12	63	22	41	17	-	30
06266-53125X30	L	light grey RAL 7035	3	M12	63	22	41	17	-	30
06266-53126X30	L	traffic red RAL 3020	3	M12	63	22	41	17	-	30
06266-53127X30	L	colza yellow RAL 1021	3	M12	63	22	41	17	-	30
06266-5312X60	L	black grey RAL 7021	3	M12	63	22	41	17	-	60
06266-53121X60	L	orange RAL 2004	3	M12	63	22	41	17	-	60
06266-53122X60	L	signal green RAL6032	3	M12	63	22	41	17	-	60
06266-53123X60	L	blue RAL5017	3	M12	63	22	41	17	-	60
06266-53125X60	L	light grey RAL 7035	3	M12	63	22	41	17	-	60
06266-53126X60	L	traffic red RAL 3020	3	M12	63	22	41	17	-	60
06266-53127X60	L	colza yellow RAL 1021	3	M12	63	22	41	17	-	60