

Item description/product images

**Description****Material:**

Black thermoplastic.

Screw grade 5.8 steel or 1.4305 stainless steel.

Version:


Steel trivalent blue passivated, stainless steel bright.



Item description/product images



Drawings



Overview of items

Order No.	Component material	Colour Cap	D	D1	D2	D3	H	H1	L
06242-AEX10	steel	black grey RAL 7021	8-32	21	12	19	21	10	10
06242-AE5X10	steel	light grey RAL 7035	8-32	21	12	19	21	10	10
06242-AE6X10	steel	traffic red RAL 3020	8-32	21	12	19	21	10	10
06242-AE7X10	steel	colza yellow RAL 1021	8-32	21	12	19	21	10	10
06242-AEX20	steel	black grey RAL 7021	8-32	21	12	19	21	10	20
06242-AE5X20	steel	light grey RAL 7035	8-32	21	12	19	21	10	20
06242-AE6X20	steel	traffic red RAL 3020	8-32	21	12	19	21	10	20
06242-AE7X20	steel	colza yellow RAL 1021	8-32	21	12	19	21	10	20
06242-A1X10	steel	black grey RAL 7021	10-32	21	12	19	21	10	10
06242-A15X10	steel	light grey RAL 7035	10-32	21	12	19	21	10	10
06242-A16X10	steel	traffic red RAL 3020	10-32	21	12	19	21	10	10
06242-A17X10	steel	colza yellow RAL 1021	10-32	21	12	19	21	10	10
06242-A1X20	steel	black grey RAL 7021	10-32	21	12	19	21	10	20
06242-A15X20	steel	light grey RAL 7035	10-32	21	12	19	21	10	20
06242-A16X20	steel	traffic red RAL 3020	10-32	21	12	19	21	10	20
06242-A17X20	steel	colza yellow RAL 1021	10-32	21	12	19	21	10	20
06242-A2X20	steel	black grey RAL 7021	1/4-20	25	14	23	25	12	20
06242-A25X20	steel	light grey RAL 7035	1/4-20	25	14	23	25	12	20
06242-A26X20	steel	traffic red RAL 3020	1/4-20	25	14	23	25	12	20
06242-A27X20	steel	colza yellow RAL 1021	1/4-20	25	14	23	25	12	20
06242-A2X30	steel	black grey RAL 7021	1/4-20	25	14	23	25	12	30
06242-A25X30	steel	light grey RAL 7035	1/4-20	25	14	23	25	12	30
06242-A26X30	steel	traffic red RAL 3020	1/4-20	25	14	23	25	12	30
06242-A27X30	steel	colza yellow RAL 1021	1/4-20	25	14	23	25	12	30
06242-A3X20	steel	black grey RAL 7021	5/16-18	33	18	31	33	15	20
06242-A35X20	steel	light grey RAL 7035	5/16-18	33	18	31	33	15	20

Overview of items

Order No.	Component material	Colour Cap	D	D1	D2	D3	H	H1	L
06242-A36X20	steel	traffic red RAL 3020	5/16-18	33	18	31	33	15	20
06242-A37X20	steel	colza yellow RAL 1021	5/16-18	33	18	31	33	15	20
06242-A3X40	steel	black grey RAL 7021	5/16-18	33	18	31	33	15	40
06242-A35X40	steel	light grey RAL 7035	5/16-18	33	18	31	33	15	40
06242-A36X40	steel	traffic red RAL 3020	5/16-18	33	18	31	33	15	40
06242-A37X40	steel	colza yellow RAL 1021	5/16-18	33	18	31	33	15	40
06242-0AEX10	stainless steel	black grey RAL 7021	8-32	21	12	19	21	10	10
06242-0AE5X10	stainless steel	light grey RAL 7035	8-32	21	12	19	21	10	10
06242-0AE6X10	stainless steel	traffic red RAL 3020	8-32	21	12	19	21	10	10
06242-0AE7X10	stainless steel	colza yellow RAL 1021	8-32	21	12	19	21	10	10
06242-0AEX20	stainless steel	black grey RAL 7021	8-32	21	12	19	21	10	20
06242-0AE5X20	stainless steel	light grey RAL 7035	8-32	21	12	19	21	10	20
06242-0AE6X20	stainless steel	traffic red RAL 3020	8-32	21	12	19	21	10	20
06242-0AE7X20	stainless steel	colza yellow RAL 1021	8-32	21	12	19	21	10	20
06242-0A1X10	stainless steel	black grey RAL 7021	10-32	21	12	19	21	10	10
06242-0A15X10	stainless steel	light grey RAL 7035	10-32	21	12	19	21	10	10
06242-0A16X10	stainless steel	traffic red RAL 3020	10-32	21	12	19	21	10	10
06242-0A17X10	stainless steel	colza yellow RAL 1021	10-32	21	12	19	21	10	10
06242-0A1X20	stainless steel	black grey RAL 7021	10-32	21	12	19	21	10	20
06242-0A15X20	stainless steel	light grey RAL 7035	10-32	21	12	19	21	10	20
06242-0A16X20	stainless steel	traffic red RAL 3020	10-32	21	12	19	21	10	20
06242-0A17X20	stainless steel	colza yellow RAL 1021	10-32	21	12	19	21	10	20
06242-0A2X20	stainless steel	black grey RAL 7021	1/4-20	25	14	23	25	12	20
06242-0A25X20	stainless steel	light grey RAL 7035	1/4-20	25	14	23	25	12	20
06242-0A26X20	stainless steel	traffic red RAL 3020	1/4-20	25	14	23	25	12	20
06242-0A27X20	stainless steel	colza yellow RAL 1021	1/4-20	25	14	23	25	12	20
06242-0A2X30	stainless steel	black grey RAL 7021	1/4-20	25	14	23	25	12	30
06242-0A25X30	stainless steel	light grey RAL 7035	1/4-20	25	14	23	25	12	30
06242-0A26X30	stainless steel	traffic red RAL 3020	1/4-20	25	14	23	25	12	30
06242-0A27X30	stainless steel	colza yellow RAL 1021	1/4-20	25	14	23	25	12	30
06242-0A3X20	stainless steel	black grey RAL 7021	5/16-18	33	18	31	33	15	20
06242-0A35X20	stainless steel	light grey RAL 7035	5/16-18	33	18	31	33	15	20
06242-0A36X20	stainless steel	traffic red RAL 3020	5/16-18	33	18	31	33	15	20
06242-0A37X20	stainless steel	colza yellow RAL 1021	5/16-18	33	18	31	33	15	20
06242-0A3X40	stainless steel	black grey RAL 7021	5/16-18	33	18	31	33	15	40
06242-0A35X40	stainless steel	light grey RAL 7035	5/16-18	33	18	31	33	15	40
06242-0A36X40	stainless steel	traffic red RAL 3020	5/16-18	33	18	31	33	15	40
06242-0A37X40	stainless steel	colza yellow RAL 1021	5/16-18	33	18	31	33	15	40