

## Item description/product images



## Description

## Material:

Stainless steel 1.4301.

## Version:

Bright.


## Note:

\*A in mm by housing length H=26.1 mm.

## Accessory:

Quarter-turn lock zinc, for fire services, DIN 14925 05578-10.

## Drawings



## Overview of items

| Order No.        | Version 1    | Version 2        | A at H=26.1 | B    | B1  | L  | Suitable for |
|------------------|--------------|------------------|-------------|------|-----|----|--------------|
| 05578-12-145X521 | without stop | offset downwards | 52,1        | 19,5 | 8,1 | 45 | -            |
| 05578-12-145X501 | without stop | offset downwards | 50,1        | 19,5 | 8,1 | 45 | -            |
| 05578-12-145X481 | without stop | offset downwards | 48,1        | 19,5 | 8,1 | 45 | -            |
| 05578-12-145X461 | without stop | offset downwards | 46,1        | 19,5 | 8,1 | 45 | -            |
| 05578-12-145X441 | without stop | offset downwards | 44,1        | 19,5 | 8,1 | 45 | -            |
| 05578-12-145X421 | without stop | offset downwards | 42,1        | 19,5 | 8,1 | 45 | -            |
| 05578-12-145X401 | without stop | offset downwards | 40,1        | 19,5 | 8,1 | 45 | -            |
| 05578-12-145X381 | without stop | offset downwards | 38,1        | 19,5 | 8,1 | 45 | -            |
| 05578-12-145X361 | without stop | offset downwards | 36,1        | 19,5 | 8,1 | 45 | -            |
| 05578-12-145X341 | without stop | offset downwards | 34,1        | 19,5 | 8,1 | 45 | -            |
| 05578-12-145X321 | without stop | offset downwards | 32,1        | 19,5 | 8,1 | 45 | -            |
| 05578-12-145X301 | without stop | offset downwards | 30,1        | 19,5 | 8,1 | 45 | -            |
| 05578-12-145X281 | without stop | offset downwards | 28,1        | 19,5 | 8,1 | 45 | -            |
| 05578-12-145X261 | without stop | straight         | 26,1        | 19,5 | 8,1 | 45 | -            |
| 05578-12-145X241 | without stop | offset upwards   | 24,1        | 19,5 | 8,1 | 45 | -            |
| 05578-12-145X221 | without stop | offset upwards   | 22,1        | 19,5 | 8,1 | 45 | -            |

## Overview of items

| Order No.        | Version 1    | Version 2      | A at H=26.1 | B    | B1  | L  | Suitable for |
|------------------|--------------|----------------|-------------|------|-----|----|--------------|
| 05578-12-145X201 | without stop | offset upwards | 20,1        | 19,5 | 8,1 | 45 | -            |
| 05578-12-145X181 | without stop | offset upwards | 18,1        | 19,5 | 8,1 | 45 | -            |
| 05578-12-145X161 | without stop | offset upwards | 16,1        | 19,5 | 8,1 | 45 | -            |
| 05578-12-145X141 | without stop | offset upwards | 14,1        | 19,5 | 8,1 | 45 | -            |
| 05578-12-145X121 | without stop | offset upwards | 12,1        | 19,5 | 8,1 | 45 | -            |