## Item description/product images




## Description

**Material:**
Black grey thermoplastic.
Threaded pin steel 5.8 or stainless steel 1.4305.

**Version:**
Steel trivalent blue passivated, stainless steel bright.

## Drawings



## Overview of items

| Order No. | Material | Colour Cap | D | D1 | D2 | D3 | H | H1 | L |
|---|---|---|---|---|---|---|---|---|---|
| 06092-105X10 | steel | black grey RAL 7021 | M5 | 21 | 14 | 19 | 22 | 8 | 10 |
| 06092-1051X10 | steel | orange RAL 2004 | M5 | 21 | 14 | 19 | 22 | 8 | 10 |
| 06092-1052X10 | steel | signal green RAL 6032 | M5 | 21 | 14 | 19 | 22 | 8 | 10 |
| 06092-1053X10 | steel | blue RAL5017 | M5 | 21 | 14 | 19 | 22 | 8 | 10 |
| 06092-1055X10 | steel | light grey RAL 7035 | M5 | 21 | 14 | 19 | 22 | 8 | 10 |
| 06092-1056X10 | steel | traffic red RAL 3020 | M5 | 21 | 14 | 19 | 22 | 8 | 10 |
| 06092-1057X10 | steel | colza yellow RAL 1021 | M5 | 21 | 14 | 19 | 22 | 8 | 10 |
| 06092-105X12 | steel | black grey RAL 7021 | M5 | 21 | 14 | 19 | 22 | 8 | 12 |
| 06092-1051X12 | steel | orange RAL 2004 | M5 | 21 | 14 | 19 | 22 | 8 | 12 |
| 06092-1052X12 | steel | signal green RAL 6032 | M5 | 21 | 14 | 19 | 22 | 8 | 12 |
| 06092-1053X12 | steel | blue RAL5017 | M5 | 21 | 14 | 19 | 22 | 8 | 12 |
| 06092-1055X12 | steel | light grey RAL 7035 | M5 | 21 | 14 | 19 | 22 | 8 | 12 |
| 06092-1056X12 | steel | traffic red RAL 3020 | M5 | 21 | 14 | 19 | 22 | 8 | 12 |
| 06092-1057X12 | steel | colza yellow RAL 1021 | M5 | 21 | 14 | 19 | 22 | 8 | 12 |
| 06092-105X15 | steel | black grey RAL 7021 | M5 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-1051X15 | steel | orange RAL 2004 | M5 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-1052X15 | steel | signal green RAL 6032 | M5 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-1053X15 | steel | blue RAL5017 | M5 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-1055X15 | steel | light grey RAL 7035 | M5 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-1056X15 | steel | traffic red RAL 3020 | M5 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-1057X15 | steel | colza yellow RAL 1021 | M5 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-105X20 | steel | black grey RAL 7021 | M5 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-1051X20 | steel | orange RAL 2004 | M5 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-1052X20 | steel | signal green RAL 6032 | M5 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-1053X20 | steel | blue RAL5017 | M5 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-1055X20 | steel | light grey RAL 7035 | M5 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-1056X20 | steel | traffic red RAL 3020 | M5 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-1057X20 | steel | colza yellow RAL 1021 | M5 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-105X25 | steel | black grey RAL 7021 | M5 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-1051X25 | steel | orange RAL 2004 | M5 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-1052X25 | steel | signal green RAL 6032 | M5 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-1053X25 | steel | blue RAL5017 | M5 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-1055X25 | steel | light grey RAL 7035 | M5 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-1056X25 | steel | traffic red RAL 3020 | M5 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-1057X25 | steel | colza yellow RAL 1021 | M5 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-106X15 | steel | black grey RAL 7021 | M6 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-1061X15 | steel | orange RAL 2004 | M6 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-1062X15 | steel | signal green RAL 6032 | M6 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-1063X15 | steel | blue RAL5017 | M6 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-1065X15 | steel | light grey RAL 7035 | M6 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-1066X15 | steel | traffic red RAL 3020 | M6 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-1067X15 | steel | colza yellow RAL 1021 | M6 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-106X20 | steel | black grey RAL 7021 | M6 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-1061X20 | steel | orange RAL 2004 | M6 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-1062X20 | steel | signal green RAL 6032 | M6 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-1063X20 | steel | blue RAL5017 | M6 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-1065X20 | steel | light grey RAL 7035 | M6 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-1066X20 | steel | traffic red RAL 3020 | M6 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-1067X20 | steel | colza yellow RAL 1021 | M6 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-106X25 | steel | black grey RAL 7021 | M6 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-1061X25 | steel | orange RAL 2004 | M6 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-1062X25 | steel | signal green RAL 6032 | M6 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-1063X25 | steel | blue RAL5017 | M6 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-1065X25 | steel | light grey RAL 7035 | M6 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-1066X25 | steel | traffic red RAL 3020 | M6 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-1067X25 | steel | colza yellow RAL 1021 | M6 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-106X30 | steel | black grey RAL 7021 | M6 | 21 | 14 | 19 | 22 | 8 | 30 |
| 06092-1061X30 | steel | orange RAL 2004 | M6 | 21 | 14 | 19 | 22 | 8 | 30 |
| 06092-1062X30 | steel | signal green RAL 6032 | M6 | 21 | 14 | 19 | 22 | 8 | 30 |
| 06092-1063X30 | steel | blue RAL5017 | M6 | 21 | 14 | 19 | 22 | 8 | 30 |
| 06092-1065X30 | steel | light grey RAL 7035 | M6 | 21 | 14 | 19 | 22 | 8 | 30 |
| 06092-1066X30 | steel | traffic red RAL 3020 | M6 | 21 | 14 | 19 | 22 | 8 | 30 |
| 06092-1067X30 | steel | colza yellow RAL 1021 | M6 | 21 | 14 | 19 | 22 | 8 | 30 |
| 06092-208X20 | steel | black grey RAL 7021 | M8 | 26 | 18 | 23 | 26 | 9,5 | 20 |
| 06092-2081X20 | steel | orange RAL 2004 | M8 | 26 | 18 | 23 | 26 | 9,5 | 20 |

## Overview of items

| Order No. | Material | Colour Cap | D | D1 | D2 | D3 | H | H1 | L |
|---|---|---|---|---|---|---|---|---|---|
| 06092-2082X20 | steel | signal green RAL 6032 | M8 | 26 | 18 | 23 | 26 | 9,5 | 20 |
| 06092-2083X20 | steel | blue RAL5017 | M8 | 26 | 18 | 23 | 26 | 9,5 | 20 |
| 06092-2085X20 | steel | light grey RAL 7035 | M8 | 26 | 18 | 23 | 26 | 9,5 | 20 |
| 06092-2086X20 | steel | traffic red RAL 3020 | M8 | 26 | 18 | 23 | 26 | 9,5 | 20 |
| 06092-2087X20 | steel | colza yellow RAL 1021 | M8 | 26 | 18 | 23 | 26 | 9,5 | 20 |
| 06092-208X25 | steel | black grey RAL 7021 | M8 | 26 | 18 | 23 | 26 | 9,5 | 25 |
| 06092-2081X25 | steel | orange RAL 2004 | M8 | 26 | 18 | 23 | 26 | 9,5 | 25 |
| 06092-2082X25 | steel | signal green RAL 6032 | M8 | 26 | 18 | 23 | 26 | 9,5 | 25 |
| 06092-2083X25 | steel | blue RAL5017 | M8 | 26 | 18 | 23 | 26 | 9,5 | 25 |
| 06092-2085X25 | steel | light grey RAL 7035 | M8 | 26 | 18 | 23 | 26 | 9,5 | 25 |
| 06092-2086X25 | steel | traffic red RAL 3020 | M8 | 26 | 18 | 23 | 26 | 9,5 | 25 |
| 06092-2087X25 | steel | colza yellow RAL 1021 | M8 | 26 | 18 | 23 | 26 | 9,5 | 25 |
| 06092-208X30 | steel | black grey RAL 7021 | M8 | 26 | 18 | 23 | 26 | 9,5 | 30 |
| 06092-2081X30 | steel | orange RAL 2004 | M8 | 26 | 18 | 23 | 26 | 9,5 | 30 |
| 06092-2082X30 | steel | signal green RAL 6032 | M8 | 26 | 18 | 23 | 26 | 9,5 | 30 |
| 06092-2083X30 | steel | blue RAL5017 | M8 | 26 | 18 | 23 | 26 | 9,5 | 30 |
| 06092-2085X30 | steel | light grey RAL 7035 | M8 | 26 | 18 | 23 | 26 | 9,5 | 30 |
| 06092-2086X30 | steel | traffic red RAL 3020 | M8 | 26 | 18 | 23 | 26 | 9,5 | 30 |
| 06092-2087X30 | steel | colza yellow RAL 1021 | M8 | 26 | 18 | 23 | 26 | 9,5 | 30 |
| 06092-208X40 | steel | black grey RAL 7021 | M8 | 26 | 18 | 23 | 26 | 9,5 | 40 |
| 06092-2081X40 | steel | orange RAL 2004 | M8 | 26 | 18 | 23 | 26 | 9,5 | 40 |
| 06092-2082X40 | steel | signal green RAL 6032 | M8 | 26 | 18 | 23 | 26 | 9,5 | 40 |
| 06092-2083X40 | steel | blue RAL5017 | M8 | 26 | 18 | 23 | 26 | 9,5 | 40 |
| 06092-2085X40 | steel | light grey RAL 7035 | M8 | 26 | 18 | 23 | 26 | 9,5 | 40 |
| 06092-2086X40 | steel | traffic red RAL 3020 | M8 | 26 | 18 | 23 | 26 | 9,5 | 40 |
| 06092-2087X40 | steel | colza yellow RAL 1021 | M8 | 26 | 18 | 23 | 26 | 9,5 | 40 |
| 06092-310X20 | steel | black grey RAL 7021 | M10 | 34 | 22 | 31 | 36 | 13 | 20 |
| 06092-3101X20 | steel | orange RAL 2004 | M10 | 34 | 22 | 31 | 36 | 13 | 20 |
| 06092-3102X20 | steel | signal green RAL 6032 | M10 | 34 | 22 | 31 | 36 | 13 | 20 |
| 06092-3103X20 | steel | blue RAL5017 | M10 | 34 | 22 | 31 | 36 | 13 | 20 |
| 06092-3105X20 | steel | light grey RAL 7035 | M10 | 34 | 22 | 31 | 36 | 13 | 20 |
| 06092-3106X20 | steel | traffic red RAL 3020 | M10 | 34 | 22 | 31 | 36 | 13 | 20 |
| 06092-3107X20 | steel | colza yellow RAL 1021 | M10 | 34 | 22 | 31 | 36 | 13 | 20 |
| 06092-310X30 | steel | black grey RAL 7021 | M10 | 34 | 22 | 31 | 36 | 13 | 30 |
| 06092-3101X30 | steel | orange RAL 2004 | M10 | 34 | 22 | 31 | 36 | 13 | 30 |
| 06092-3102X30 | steel | signal green RAL 6032 | M10 | 34 | 22 | 31 | 36 | 13 | 30 |
| 06092-3103X30 | steel | blue RAL5017 | M10 | 34 | 22 | 31 | 36 | 13 | 30 |
| 06092-3105X30 | steel | light grey RAL 7035 | M10 | 34 | 22 | 31 | 36 | 13 | 30 |
| 06092-3106X30 | steel | traffic red RAL 3020 | M10 | 34 | 22 | 31 | 36 | 13 | 30 |
| 06092-3107X30 | steel | colza yellow RAL 1021 | M10 | 34 | 22 | 31 | 36 | 13 | 30 |
| 06092-310X40 | steel | black grey RAL 7021 | M10 | 34 | 22 | 31 | 36 | 13 | 40 |
| 06092-3101X40 | steel | orange RAL 2004 | M10 | 34 | 22 | 31 | 36 | 13 | 40 |
| 06092-3102X40 | steel | signal green RAL 6032 | M10 | 34 | 22 | 31 | 36 | 13 | 40 |
| 06092-3103X40 | steel | blue RAL5017 | M10 | 34 | 22 | 31 | 36 | 13 | 40 |
| 06092-3105X40 | steel | light grey RAL 7035 | M10 | 34 | 22 | 31 | 36 | 13 | 40 |
| 06092-3106X40 | steel | traffic red RAL 3020 | M10 | 34 | 22 | 31 | 36 | 13 | 40 |
| 06092-3107X40 | steel | colza yellow RAL 1021 | M10 | 34 | 22 | 31 | 36 | 13 | 40 |
| 06092-0105X10 | stainless steel | black grey RAL 7021 | M5 | 21 | 14 | 19 | 22 | 8 | 10 |
| 06092-01051X10 | stainless steel | orange RAL 2004 | M5 | 21 | 14 | 19 | 22 | 8 | 10 |
| 06092-01052X10 | stainless steel | signal green RAL 6032 | M5 | 21 | 14 | 19 | 22 | 8 | 10 |
| 06092-01053X10 | stainless steel | blue RAL5017 | M5 | 21 | 14 | 19 | 22 | 8 | 10 |
| 06092-01055X10 | stainless steel | light grey RAL 7035 | M5 | 21 | 14 | 19 | 22 | 8 | 10 |
| 06092-01056X10 | stainless steel | traffic red RAL 3020 | M5 | 21 | 14 | 19 | 22 | 8 | 10 |
| 06092-01057X10 | stainless steel | colza yellow RAL 1021 | M5 | 21 | 14 | 19 | 22 | 8 | 10 |
| 06092-0105X12 | stainless steel | black grey RAL 7021 | M5 | 21 | 14 | 19 | 22 | 8 | 12 |
| 06092-01051X12 | stainless steel | orange RAL 2004 | M5 | 21 | 14 | 19 | 22 | 8 | 12 |
| 06092-01052X12 | stainless steel | signal green RAL 6032 | M5 | 21 | 14 | 19 | 22 | 8 | 12 |
| 06092-01053X12 | stainless steel | blue RAL5017 | M5 | 21 | 14 | 19 | 22 | 8 | 12 |
| 06092-01055X12 | stainless steel | light grey RAL 7035 | M5 | 21 | 14 | 19 | 22 | 8 | 12 |
| 06092-01056X12 | stainless steel | traffic red RAL 3020 | M5 | 21 | 14 | 19 | 22 | 8 | 12 |
| 06092-01057X12 | stainless steel | colza yellow RAL 1021 | M5 | 21 | 14 | 19 | 22 | 8 | 12 |
| 06092-0105X15 | stainless steel | black grey RAL 7021 | M5 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-01051X15 | stainless steel | orange RAL 2004 | M5 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-01052X15 | stainless steel | signal green RAL 6032 | M5 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-01053X15 | stainless steel | blue RAL5017 | M5 | 21 | 14 | 19 | 22 | 8 | 15 |

## Overview of items

| Order No. | Material | Colour Cap | D | D1 | D2 | D3 | H | H1 | L |
|---|---|---|---|---|---|---|---|---|---|
| 06092-01055X15 | stainless steel | light grey RAL 7035 | M5 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-01056X15 | stainless steel | traffic red RAL 3020 | M5 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-01057X15 | stainless steel | colza yellow RAL 1021 | M5 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-0105X20 | stainless steel | black grey RAL 7021 | M5 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-01051X20 | stainless steel | orange RAL 2004 | M5 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-01052X20 | stainless steel | signal green RAL 6032 | M5 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-01053X20 | stainless steel | blue RAL5017 | M5 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-01055X20 | stainless steel | light grey RAL 7035 | M5 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-01056X20 | stainless steel | traffic red RAL 3020 | M5 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-01057X20 | stainless steel | colza yellow RAL 1021 | M5 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-0105X25 | stainless steel | black grey RAL 7021 | M5 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-01051X25 | stainless steel | orange RAL 2004 | M5 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-01052X25 | stainless steel | signal green RAL 6032 | M5 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-01053X25 | stainless steel | blue RAL5017 | M5 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-01055X25 | stainless steel | light grey RAL 7035 | M5 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-01056X25 | stainless steel | traffic red RAL 3020 | M5 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-01057X25 | stainless steel | colza yellow RAL 1021 | M5 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-0106X15 | stainless steel | black grey RAL 7021 | M6 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-01061X15 | stainless steel | orange RAL 2004 | M6 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-01062X15 | stainless steel | signal green RAL 6032 | M6 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-01063X15 | stainless steel | blue RAL5017 | M6 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-01065X15 | stainless steel | light grey RAL 7035 | M6 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-01066X15 | stainless steel | traffic red RAL 3020 | M6 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-01067X15 | stainless steel | colza yellow RAL 1021 | M6 | 21 | 14 | 19 | 22 | 8 | 15 |
| 06092-0106X20 | stainless steel | black grey RAL 7021 | M6 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-01061X20 | stainless steel | orange RAL 2004 | M6 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-01062X20 | stainless steel | signal green RAL 6032 | M6 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-01063X20 | stainless steel | blue RAL5017 | M6 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-01065X20 | stainless steel | light grey RAL 7035 | M6 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-01066X20 | stainless steel | traffic red RAL 3020 | M6 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-01067X20 | stainless steel | colza yellow RAL 1021 | M6 | 21 | 14 | 19 | 22 | 8 | 20 |
| 06092-0106X25 | stainless steel | black grey RAL 7021 | M6 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-01061X25 | stainless steel | orange RAL 2004 | M6 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-01062X25 | stainless steel | signal green RAL 6032 | M6 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-01063X25 | stainless steel | blue RAL5017 | M6 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-01065X25 | stainless steel | light grey RAL 7035 | M6 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-01066X25 | stainless steel | traffic red RAL 3020 | M6 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-01067X25 | stainless steel | colza yellow RAL 1021 | M6 | 21 | 14 | 19 | 22 | 8 | 25 |
| 06092-0106X30 | stainless steel | black grey RAL 7021 | M6 | 21 | 14 | 19 | 22 | 8 | 30 |
| 06092-01061X30 | stainless steel | orange RAL 2004 | M6 | 21 | 14 | 19 | 22 | 8 | 30 |
| 06092-01062X30 | stainless steel | signal green RAL 6032 | M6 | 21 | 14 | 19 | 22 | 8 | 30 |
| 06092-01063X30 | stainless steel | blue RAL5017 | M6 | 21 | 14 | 19 | 22 | 8 | 30 |
| 06092-01065X30 | stainless steel | light grey RAL 7035 | M6 | 21 | 14 | 19 | 22 | 8 | 30 |
| 06092-01066X30 | stainless steel | traffic red RAL 3020 | M6 | 21 | 14 | 19 | 22 | 8 | 30 |
| 06092-01067X30 | stainless steel | colza yellow RAL 1021 | M6 | 21 | 14 | 19 | 22 | 8 | 30 |
| 06092-0208X20 | stainless steel | black grey RAL 7021 | M8 | 26 | 18 | 23 | 26 | 9,5 | 20 |
| 06092-02081X20 | stainless steel | orange RAL 2004 | M8 | 26 | 18 | 23 | 26 | 9,5 | 20 |
| 06092-02082X20 | stainless steel | signal green RAL 6032 | M8 | 26 | 18 | 23 | 26 | 9,5 | 20 |
| 06092-02083X20 | stainless steel | blue RAL5017 | M8 | 26 | 18 | 23 | 26 | 9,5 | 20 |
| 06092-02085X20 | stainless steel | light grey RAL 7035 | M8 | 26 | 18 | 23 | 26 | 9,5 | 20 |
| 06092-02086X20 | stainless steel | traffic red RAL 3020 | M8 | 26 | 18 | 23 | 26 | 9,5 | 20 |
| 06092-02087X20 | stainless steel | colza yellow RAL 1021 | M8 | 26 | 18 | 23 | 26 | 9,5 | 20 |
| 06092-0208X25 | stainless steel | black grey RAL 7021 | M8 | 26 | 18 | 23 | 26 | 9,5 | 25 |
| 06092-02081X25 | stainless steel | orange RAL 2004 | M8 | 26 | 18 | 23 | 26 | 9,5 | 25 |
| 06092-02082X25 | stainless steel | signal green RAL 6032 | M8 | 26 | 18 | 23 | 26 | 9,5 | 25 |
| 06092-02083X25 | stainless steel | blue RAL5017 | M8 | 26 | 18 | 23 | 26 | 9,5 | 25 |
| 06092-02085X25 | stainless steel | light grey RAL 7035 | M8 | 26 | 18 | 23 | 26 | 9,5 | 25 |
| 06092-02086X25 | stainless steel | traffic red RAL 3020 | M8 | 26 | 18 | 23 | 26 | 9,5 | 25 |
| 06092-02087X25 | stainless steel | colza yellow RAL 1021 | M8 | 26 | 18 | 23 | 26 | 9,5 | 25 |
| 06092-0208X30 | stainless steel | black grey RAL 7021 | M8 | 26 | 18 | 23 | 26 | 9,5 | 30 |
| 06092-02081X30 | stainless steel | orange RAL 2004 | M8 | 26 | 18 | 23 | 26 | 9,5 | 30 |
| 06092-02082X30 | stainless steel | signal green RAL 6032 | M8 | 26 | 18 | 23 | 26 | 9,5 | 30 |
| 06092-02083X30 | stainless steel | blue RAL5017 | M8 | 26 | 18 | 23 | 26 | 9,5 | 30 |
| 06092-02085X30 | stainless steel | light grey RAL 7035 | M8 | 26 | 18 | 23 | 26 | 9,5 | 30 |
| 06092-02086X30 | stainless steel | traffic red RAL 3020 | M8 | 26 | 18 | 23 | 26 | 9,5 | 30 |

## Overview of items

| Order No. | Material | Colour Cap | D | D1 | D2 | D3 | H | H1 | L |
|---|---|---|---|---|---|---|---|---|---|
| 06092-02087X30 | stainless steel | colza yellow RAL 1021 | M8 | 26 | 18 | 23 | 26 | 9,5 | 30 |
| 06092-0208X40 | stainless steel | black grey RAL 7021 | M8 | 26 | 18 | 23 | 26 | 9,5 | 40 |
| 06092-02081X40 | stainless steel | orange RAL 2004 | M8 | 26 | 18 | 23 | 26 | 9,5 | 40 |
| 06092-02082X40 | stainless steel | signal green RAL 6032 | M8 | 26 | 18 | 23 | 26 | 9,5 | 40 |
| 06092-02083X40 | stainless steel | blue RAL5017 | M8 | 26 | 18 | 23 | 26 | 9,5 | 40 |
| 06092-02085X40 | stainless steel | light grey RAL 7035 | M8 | 26 | 18 | 23 | 26 | 9,5 | 40 |
| 06092-02086X40 | stainless steel | traffic red RAL 3020 | M8 | 26 | 18 | 23 | 26 | 9,5 | 40 |
| 06092-02087X40 | stainless steel | colza yellow RAL 1021 | M8 | 26 | 18 | 23 | 26 | 9,5 | 40 |
| 06092-0310X20 | stainless steel | black grey RAL 7021 | M10 | 34 | 22 | 31 | 36 | 13 | 20 |
| 06092-03101X20 | stainless steel | orange RAL 2004 | M10 | 34 | 22 | 31 | 36 | 13 | 20 |
| 06092-03102X20 | stainless steel | signal green RAL 6032 | M10 | 34 | 22 | 31 | 36 | 13 | 20 |
| 06092-03103X20 | stainless steel | blue RAL5017 | M10 | 34 | 22 | 31 | 36 | 13 | 20 |
| 06092-03105X20 | stainless steel | light grey RAL 7035 | M10 | 34 | 22 | 31 | 36 | 13 | 20 |
| 06092-03106X20 | stainless steel | traffic red RAL 3020 | M10 | 34 | 22 | 31 | 36 | 13 | 20 |
| 06092-03107X20 | stainless steel | colza yellow RAL 1021 | M10 | 34 | 22 | 31 | 36 | 13 | 20 |
| 06092-0310X30 | stainless steel | black grey RAL 7021 | M10 | 34 | 22 | 31 | 36 | 13 | 30 |
| 06092-03101X30 | stainless steel | orange RAL 2004 | M10 | 34 | 22 | 31 | 36 | 13 | 30 |
| 06092-03102X30 | stainless steel | signal green RAL 6032 | M10 | 34 | 22 | 31 | 36 | 13 | 30 |
| 06092-03103X30 | stainless steel | blue RAL5017 | M10 | 34 | 22 | 31 | 36 | 13 | 30 |
| 06092-03105X30 | stainless steel | light grey RAL 7035 | M10 | 34 | 22 | 31 | 36 | 13 | 30 |
| 06092-03106X30 | stainless steel | traffic red RAL 3020 | M10 | 34 | 22 | 31 | 36 | 13 | 30 |
| 06092-03107X30 | stainless steel | colza yellow RAL 1021 | M10 | 34 | 22 | 31 | 36 | 13 | 30 |
| 06092-0310X40 | stainless steel | black grey RAL 7021 | M10 | 34 | 22 | 31 | 36 | 13 | 40 |
| 06092-03101X40 | stainless steel | orange RAL 2004 | M10 | 34 | 22 | 31 | 36 | 13 | 40 |
| 06092-03102X40 | stainless steel | signal green RAL 6032 | M10 | 34 | 22 | 31 | 36 | 13 | 40 |
| 06092-03103X40 | stainless steel | blue RAL5017 | M10 | 34 | 22 | 31 | 36 | 13 | 40 |
| 06092-03105X40 | stainless steel | light grey RAL 7035 | M10 | 34 | 22 | 31 | 36 | 13 | 40 |
| 06092-03106X40 | stainless steel | traffic red RAL 3020 | M10 | 34 | 22 | 31 | 36 | 13 | 40 |
| 06092-03107X40 | stainless steel | colza yellow RAL 1021 | M10 | 34 | 22 | 31 | 36 | 13 | 40 |