



Item description/product images



Description

Material:


Thermoplastic, black grey.

Bush and screw stainless steel 1.4305.

Version:

Stainless steel bright.

Drawings



Overview of items

Order No.	Form	Colour Cap	Size	D	D1	D2	H	H1	T
06267-2105	K	black grey RAL 7021	1	M5	40	16,5	31	13	10
06267-21051	K	orange RAL 2004	1	M5	40	16,5	31	13	10
06267-21052	K	signal green RAL6032	1	M5	40	16,5	31	13	10
06267-21053	K	blue RAL5017	1	M5	40	16,5	31	13	10
06267-21055	K	light grey RAL 7035	1	M5	40	16,5	31	13	10
06267-21056	K	traffic red RAL 3020	1	M5	40	16,5	31	13	10
06267-21057	K	colza yellow RAL 1021	1	M5	40	16,5	31	13	10
06267-2106	K	black grey RAL 7021	1	M6	40	16,5	31	13	10
06267-21061	K	orange RAL 2004	1	M6	40	16,5	31	13	10
06267-21062	K	signal green RAL6032	1	M6	40	16,5	31	13	10
06267-21063	K	blue RAL5017	1	M6	40	16,5	31	13	10
06267-21065	K	light grey RAL 7035	1	M6	40	16,5	31	13	10
06267-21066	K	traffic red RAL 3020	1	M6	40	16,5	31	13	10
06267-21067	K	colza yellow RAL 1021	1	M6	40	16,5	31	13	10
06267-2108	K	black grey RAL 7021	1	M8	40	16,5	31	13	14
06267-21081	K	orange RAL 2004	1	M8	40	16,5	31	13	10
06267-21082	K	signal green RAL6032	1	M8	40	16,5	31	13	10

Overview of items

Order No.	Form	Colour Cap	Size	D	D1	D2	H	H1	T
06267-21083	K	blue RAL5017	1	M8	40	16,5	31	13	10
06267-21085	K	light grey RAL 7035	1	M8	40	16,5	31	13	14
06267-21086	K	traffic red RAL 3020	1	M8	40	16,5	31	13	14
06267-21087	K	colza yellow RAL 1021	1	M8	40	16,5	31	13	14
06267-2208	K	black grey RAL 7021	2	M8	50	18	36	15	14
06267-22081	K	orange RAL 2004	2	M8	50	18	36	15	14
06267-22082	K	signal green RAL6032	2	M8	50	18	36	15	14
06267-22083	K	blue RAL5017	2	M8	50	18	36	15	14
06267-22085	K	light grey RAL 7035	2	M8	50	18	36	15	14
06267-22086	K	traffic red RAL 3020	2	M8	50	18	36	15	14
06267-22087	K	colza yellow RAL 1021	2	M8	50	18	36	15	14
06267-2210	K	black grey RAL 7021	2	M10	50	18	36	15	14
06267-22101	K	orange RAL 2004	2	M10	50	18	36	15	14
06267-22102	K	signal green RAL6032	2	M10	50	18	36	15	14
06267-22103	K	blue RAL5017	2	M10	50	18	36	15	14
06267-22105	K	light grey RAL 7035	2	M10	50	18	36	15	14
06267-22106	K	traffic red RAL 3020	2	M10	50	18	36	15	14
06267-22107	K	colza yellow RAL 1021	2	M10	50	18	36	15	14
06267-2310	K	black grey RAL 7021	3	M10	63	22	41	17	14
06267-23101	K	orange RAL 2004	3	M10	63	22	41	17	14
06267-23102	K	signal green RAL6032	3	M10	63	22	41	17	14
06267-23103	K	blue RAL5017	3	M10	63	22	41	17	14
06267-23105	K	light grey RAL 7035	3	M10	63	22	41	17	14
06267-23106	K	traffic red RAL 3020	3	M10	63	22	41	17	14
06267-23107	K	colza yellow RAL 1021	3	M10	63	22	41	17	14
06267-2312	K	black grey RAL 7021	3	M12	63	22	41	17	18
06267-23121	K	orange RAL 2004	3	M12	63	22	41	17	18
06267-23122	K	signal green RAL6032	3	M12	63	22	41	17	18
06267-23123	K	blue RAL5017	3	M12	63	22	41	17	18
06267-23125	K	light grey RAL 7035	3	M12	63	22	41	17	18
06267-23126	K	traffic red RAL 3020	3	M12	63	22	41	17	18
06267-23127	K	colza yellow RAL 1021	3	M12	63	22	41	17	18