

Item description/product images



Description


Material:

Black thermoplastic.


Bush grade 5.8 steel or 1.4305 stainless steel.

Version:

Steel trivalent blue passivated, stainless steel bright.



Drawings



Overview of items

Order No.	Component material	Colour Cap	D	D1	D2	D3	H	H1	T
06092-104	steel	black grey RAL 7021	M4	21	14	19	22	8	10
06092-1041	steel	orange RAL 2004	M4	21	14	19	22	8	10
06092-1042	steel	signal green RAL6032	M4	21	14	19	22	8	10
06092-1043	steel	blue RAL5017	M4	21	14	19	22	8	10
06092-1045	steel	light grey RAL 7035	M4	21	14	19	22	8	10
06092-1046	steel	traffic red RAL 3020	M4	21	14	19	22	8	10
06092-1047	steel	colza yellow RAL 1021	M4	21	14	19	22	8	10
06092-105	steel	black grey RAL 7021	M5	21	14	19	22	8	10
06092-1051	steel	orange RAL 2004	M5	21	14	19	22	8	10
06092-1052	steel	signal green RAL6032	M5	21	14	19	22	8	10
06092-1053	steel	blue RAL5017	M5	21	14	19	22	8	10
06092-1055	steel	light grey RAL 7035	M5	21	14	19	22	8	10
06092-1056	steel	traffic red RAL 3020	M5	21	14	19	22	8	10
06092-1057	steel	colza yellow RAL 1021	M5	21	14	19	22	8	10
06092-106	steel	black grey RAL 7021	M6	21	14	19	22	8	10

Overview of items

Order No.	Component material	Colour Cap	D	D1	D2	D3	H	H1	T
06092-1061	steel	orange RAL 2004	M6	21	14	19	22	8	10
06092-1062	steel	signal green RAL6032	M6	21	14	19	22	8	10
06092-1063	steel	blue RAL5017	M6	21	14	19	22	8	10
06092-1065	steel	light grey RAL 7035	M6	21	14	19	22	8	10
06092-1066	steel	traffic red RAL 3020	M6	21	14	19	22	8	10
06092-1067	steel	colza yellow RAL 1021	M6	21	14	19	22	8	10
06092-208	steel	black grey RAL 7021	M8	26	18	23	26	9,5	14
06092-2081	steel	orange RAL 2004	M8	26	18	23	26	9,5	14
06092-2082	steel	signal green RAL6032	M8	26	18	23	26	9,5	14
06092-2083	steel	blue RAL5017	M8	26	18	23	26	9,5	14
06092-2085	steel	light grey RAL 7035	M8	26	18	23	26	9,5	14
06092-2086	steel	traffic red RAL 3020	M8	26	18	23	26	9,5	14
06092-2087	steel	colza yellow RAL 1021	M8	26	18	23	26	9,5	14
06092-308	steel	black grey RAL 7021	M8	34	22	31	36	13	14
06092-3081	steel	orange RAL 2004	M8	34	22	31	36	13	14
06092-3082	steel	signal green RAL6032	M8	34	22	31	36	13	14
06092-3083	steel	blue RAL5017	M8	34	22	31	36	13	14
06092-3085	steel	light grey RAL 7035	M8	34	22	31	36	13	14
06092-3086	steel	traffic red RAL 3020	M8	34	22	31	36	13	14
06092-3087	steel	colza yellow RAL 1021	M8	34	22	31	36	13	14
06092-310	steel	black grey RAL 7021	M10	34	22	31	36	13	14
06092-3101	steel	orange RAL 2004	M10	34	22	31	36	13	14
06092-3102	steel	signal green RAL6032	M10	34	22	31	36	13	14
06092-3103	steel	blue RAL5017	M10	34	22	31	36	13	14
06092-3105	steel	light grey RAL 7035	M10	34	22	31	36	13	14
06092-3106	steel	traffic red RAL 3020	M10	34	22	31	36	13	14
06092-3107	steel	colza yellow RAL 1021	M10	34	22	31	36	13	14
06092-0104	stainless steel	black grey RAL 7021	M4	21	14	19	22	8	10
06092-01041	stainless steel	orange RAL 2004	M4	21	14	19	22	8	10
06092-01042	stainless steel	signal green RAL6032	M4	21	14	19	22	8	10
06092-01043	stainless steel	blue RAL5017	M4	21	14	19	22	8	10
06092-01045	stainless steel	light grey RAL 7035	M4	21	14	19	22	8	10
06092-01046	stainless steel	traffic red RAL 3020	M4	21	14	19	22	8	10
06092-01047	stainless steel	colza yellow RAL 1021	M4	21	14	19	22	8	10
06092-0105	stainless steel	black grey RAL 7021	M5	21	14	19	22	8	10
06092-01051	stainless steel	orange RAL 2004	M5	21	14	19	22	8	10
06092-01052	stainless steel	signal green RAL6032	M5	21	14	19	22	8	10
06092-01053	stainless steel	blue RAL5017	M5	21	14	19	22	8	10
06092-01055	stainless steel	light grey RAL 7035	M5	21	14	19	22	8	10
06092-01056	stainless steel	traffic red RAL 3020	M5	21	14	19	22	8	10
06092-01057	stainless steel	colza yellow RAL 1021	M5	21	14	19	22	8	10
06092-0106	stainless steel	black grey RAL 7021	M6	21	14	19	22	8	10
06092-01061	stainless steel	orange RAL 2004	M6	21	14	19	22	8	10
06092-01062	stainless steel	signal green RAL6032	M6	21	14	19	22	8	10
06092-01063	stainless steel	blue RAL5017	M6	21	14	19	22	8	10
06092-01065	stainless steel	light grey RAL 7035	M6	21	14	19	22	8	10
06092-01066	stainless steel	traffic red RAL 3020	M6	21	14	19	22	8	10
06092-01067	stainless steel	colza yellow RAL 1021	M6	21	14	19	22	8	10
06092-0208	stainless steel	black grey RAL 7021	M8	26	18	23	26	9,5	14
06092-02081	stainless steel	orange RAL 2004	M8	26	18	23	26	9,5	14
06092-02082	stainless steel	signal green RAL6032	M8	26	18	23	26	9,5	14
06092-02083	stainless steel	blue RAL5017	M8	26	18	23	26	9,5	14
06092-02085	stainless steel	light grey RAL 7035	M8	26	18	23	26	9,5	14
06092-02086	stainless steel	traffic red RAL 3020	M8	26	18	23	26	9,5	14
06092-02087	stainless steel	colza yellow RAL 1021	M8	26	18	23	26	9,5	14
06092-0308	stainless steel	black grey RAL 7021	M8	34	22	31	36	13	14
06092-03081	stainless steel	orange RAL 2004	M8	34	22	31	36	13	14
06092-03082	stainless steel	signal green RAL6032	M8	34	22	31	36	13	14
06092-03083	stainless steel	blue RAL5017	M8	34	22	31	36	13	14
06092-03085	stainless steel	light grey RAL 7035	M8	34	22	31	36	13	14
06092-03086	stainless steel	traffic red RAL 3020	M8	34	22	31	36	13	14
06092-03087	stainless steel	colza yellow RAL 1021	M8	34	22	31	36	13	14
06092-0310	stainless steel	black grey RAL 7021	M10	34	22	31	36	13	14
06092-03101	stainless steel	orange RAL 2004	M10	34	22	31	36	13	14
06092-03102	stainless steel	signal green RAL6032	M10	34	22	31	36	13	14

Overview of items

Order No.	Component material	Colour Cap	D	D1	D2	D3	H	H1	T
06092-03103	stainless steel	blue RAL5017	M10	34	22	31	36	13	14
06092-03105	stainless steel	light grey RAL 7035	M10	34	22	31	36	13	14
06092-03106	stainless steel	traffic red RAL 3020	M10	34	22	31	36	13	14
06092-03107	stainless steel	colza yellow RAL 1021	M10	34	22	31	36	13	14