

Item description/product images



Description

Material:

Steel or stainless steel A2.

Version:

Grade 4.6, electro zinc-plated.

Grade 8.8 bright or electro zinc-plated.

Bright stainless steel.


Note:

Threaded rods are only available in 1000 mm lengths.

Threaded rods size M3 and M4 may be slightly bent when delivered.

The blank version may, for technical reasons have a grey to black surface.

Drawings



Overview of items

Order No.	Main material	Surface finish body	Version 1	Grade	D	L
07640-031	steel	galvanised	RH thread	4.6	M3	1000
07640-041	steel	galvanised	RH thread	4.6	M4	1000
07640-051	steel	galvanised	RH thread	4.6	M5	1000
07640-061	steel	galvanised	RH thread	4.6	M6	1000
07640-081	steel	galvanised	RH thread	4.6	M8	1000
07640-101	steel	galvanised	RH thread	4.6	M10	1000
07640-121	steel	galvanised	RH thread	4.6	M12	1000
07640-161	steel	galvanised	RH thread	4.6	M16	1000
07640-201	steel	galvanised	RH thread	4.6	M20	1000
07640-241	steel	galvanised	RH thread	4.6	M24	1000
07640-301	steel	galvanised	RH thread	4.6	M30	1000
07640-361	steel	galvanised	RH thread	4.6	M36	1000
07640-1041	steel	galvanised	LH thread	4.6	M4	1000
07640-1051	steel	galvanised	LH thread	4.6	M5	1000
07640-1061	steel	galvanised	LH thread	4.6	M6	1000
07640-1081	steel	galvanised	LH thread	4.6	M8	1000
07640-1101	steel	galvanised	LH thread	4.6	M10	1000
07640-1121	steel	galvanised	LH thread	4.6	M12	1000
07640-1161	steel	galvanised	LH thread	4.6	M16	1000
07640-1201	steel	galvanised	LH thread	4.6	M20	1000
07640-1241	steel	galvanised	LH thread	4.6	M24	1000
07640-1301	steel	galvanised	LH thread	4.6	M30	1000
07640-05	steel	bright	RH thread	8.8	M5	1000
07640-06	steel	bright	RH thread	8.8	M6	1000
07640-08	steel	bright	RH thread	8.8	M8	1000
07640-10	steel	bright	RH thread	8.8	M10	1000
07640-12	steel	bright	RH thread	8.8	M12	1000
07640-14	steel	bright	RH thread	8.8	M14	1000
07640-16	steel	bright	RH thread	8.8	M16	1000
07640-18	steel	bright	RH thread	8.8	M18	1000

Overview of items

Order No.	Main material	Surface finish body	Version 1	Grade	D	L
07640-20	steel	bright	RH thread	8.8	M20	1000
07640-22	steel	bright	RH thread	8.8	M22	1000
07640-24	steel	bright	RH thread	8.8	M24	1000
07640-043	steel	galvanised	RH thread	8.8	M4	1000
07640-053	steel	galvanised	RH thread	8.8	M5	1000
07640-063	steel	galvanised	RH thread	8.8	M6	1000
07640-083	steel	galvanised	RH thread	8.8	M8	1000
07640-103	steel	galvanised	RH thread	8.8	M10	1000
07640-123	steel	galvanised	RH thread	8.8	M12	1000
07640-143	steel	galvanised	RH thread	8.8	M14	1000
07640-163	steel	galvanised	RH thread	8.8	M16	1000
07640-183	steel	galvanised	RH thread	8.8	M18	1000
07640-203	steel	galvanised	RH thread	8.8	M20	1000
07640-223	steel	galvanised	RH thread	8.8	M22	1000
07640-243	steel	galvanised	RH thread	8.8	M24	1000
07640-303	steel	galvanised	RH thread	8.8	M30	1000
07640-363	steel	galvanised	RH thread	8.8	M36	1000
07640-1063	steel	galvanised	LH thread	8.8	M6	1000
07640-1083	steel	galvanised	LH thread	8.8	M8	1000
07640-1103	steel	galvanised	LH thread	8.8	M10	1000
07640-1123	steel	galvanised	LH thread	8.8	M12	1000
07640-1163	steel	galvanised	LH thread	8.8	M16	1000
07640-1203	steel	galvanised	LH thread	8.8	M20	1000
07640-1243	steel	galvanised	LH thread	8.8	M24	1000
07640-1303	steel	galvanised	LH thread	8.8	M30	1000
07640-1363	steel	galvanised	LH thread	8.8	M36	1000
07640-052	stainless steel A2	bright	RH thread	70	M5	1000
07640-062	stainless steel A2	bright	RH thread	70	M6	1000
07640-082	stainless steel A2	bright	RH thread	70	M8	1000
07640-102	stainless steel A2	bright	RH thread	70	M10	1000
07640-122	stainless steel A2	bright	RH thread	70	M12	1000
07640-162	stainless steel A2	bright	RH thread	70	M16	1000
07640-182	stainless steel A2	bright	RH thread	70	M18	1000
07640-202	stainless steel A2	bright	RH thread	70	M20	1000
07640-222	stainless steel A2	bright	RH thread	70	M22	1000
07640-242	stainless steel A2	bright	RH thread	70	M24	1000
07640-1042	stainless steel A2	bright	LH thread	70	M4	1000
07640-1052	stainless steel A2	bright	LH thread	70	M5	1000
07640-1062	stainless steel A2	bright	LH thread	70	M6	1000
07640-1082	stainless steel A2	bright	LH thread	70	M8	1000
07640-1102	stainless steel A2	bright	LH thread	70	M10	1000
07640-1122	stainless steel A2	bright	LH thread	70	M12	1000
07640-1162	stainless steel A2	bright	LH thread	70	M16	1000
07640-1202	stainless steel A2	bright	LH thread	70	M20	1000
07640-1242	stainless steel A2	bright	LH thread	70	M24	1000