


Item description/product images



Description

Material:


Black thermoplastic.

Bush grade 5.8 steel or 1.4305 stainless steel.

Version:

Steel trivalent blue passivated, stainless steel bright.

Drawings



Overview of items

Order No.	Component material	Colour Cap	D	D1	D2	D3	H	H1	T
06241-004	stainless steel	black grey RAL 7021	M4	21	12	19	21	10	10
06241-0041	stainless steel	orange RAL 2004	M4	21	12	19	21	10	10
06241-0046	stainless steel	traffic red RAL 3020	M4	21	12	19	21	10	10
06241-0042	stainless steel	signal green RAL6032	M4	21	12	19	21	10	10
06241-0047	stainless steel	colza yellow RAL 1021	M4	21	12	19	21	10	10
06241-0043	stainless steel	blue RAL5017	M4	21	12	19	21	10	10
06241-0045	stainless steel	light grey RAL 7035	M4	21	12	19	21	10	10
06241-0051	stainless steel	orange RAL 2004	M5	21	12	19	21	10	10
06241-0052	stainless steel	signal green RAL6032	M5	21	12	19	21	10	10
06241-005	stainless steel	black grey RAL 7021	M5	21	12	19	21	10	10
06241-0053	stainless steel	blue RAL5017	M5	21	12	19	21	10	10
06241-0057	stainless steel	colza yellow RAL 1021	M5	21	12	19	21	10	10
06241-0055	stainless steel	light grey RAL 7035	M5	21	12	19	21	10	10
06241-0056	stainless steel	traffic red RAL 3020	M5	21	12	19	21	10	10
06241-0067	stainless steel	colza yellow RAL 1021	M6	25	14	23	25	12	10
06241-0065	stainless steel	light grey RAL 7035	M6	25	14	23	25	12	10
06241-0063	stainless steel	blue RAL5017	M6	25	14	23	25	12	10

Overview of items

Order No.	Component material	Colour Cap	D	D1	D2	D3	H	H1	T
06241-0062	stainless steel	signal green RAL6032	M6	25	14	23	25	12	10
06241-0061	stainless steel	orange RAL 2004	M6	25	14	23	25	12	10
06241-006	stainless steel	black grey RAL 7021	M6	25	14	23	25	12	10
06241-0066	stainless steel	traffic red RAL 3020	M6	25	14	23	25	12	10
06241-0086	stainless steel	traffic red RAL 3020	M8	33	18	31	33	15	14
06241-0085	stainless steel	light grey RAL 7035	M8	33	18	31	33	15	14
06241-0083	stainless steel	blue RAL5017	M8	33	18	31	33	15	14
06241-0082	stainless steel	signal green RAL6032	M8	33	18	31	33	15	14
06241-0081	stainless steel	orange RAL 2004	M8	33	18	31	33	15	14
06241-008	stainless steel	black grey RAL 7021	M8	33	18	31	33	15	14
06241-0087	stainless steel	colza yellow RAL 1021	M8	33	18	31	33	15	14
06241-041	steel	orange RAL 2004	M4	21	12	19	21	10	10
06241-042	steel	signal green RAL6032	M4	21	12	19	21	10	10
06241-04	steel	black grey RAL 7021	M4	21	12	19	21	10	10
06241-043	steel	blue RAL5017	M4	21	12	19	21	10	10
06241-047	steel	colza yellow RAL 1021	M4	21	12	19	21	10	10
06241-045	steel	light grey RAL 7035	M4	21	12	19	21	10	10
06241-046	steel	traffic red RAL 3020	M4	21	12	19	21	10	10
06241-056	steel	traffic red RAL 3020	M5	21	12	19	21	10	10
06241-055	steel	light grey RAL 7035	M5	21	12	19	21	10	10
06241-057	steel	colza yellow RAL 1021	M5	21	12	19	21	10	10
06241-053	steel	blue RAL5017	M5	21	12	19	21	10	10
06241-05	steel	black grey RAL 7021	M5	21	12	19	21	10	10
06241-052	steel	signal green RAL6032	M5	21	12	19	21	10	10
06241-051	steel	orange RAL 2004	M5	21	12	19	21	10	10
06241-061	steel	orange RAL 2004	M6	25	14	23	25	12	10
06241-067	steel	colza yellow RAL 1021	M6	25	14	23	25	12	10
06241-06	steel	black grey RAL 7021	M6	25	14	23	25	12	10
06241-066	steel	traffic red RAL 3020	M6	25	14	23	25	12	10
06241-062	steel	signal green RAL6032	M6	25	14	23	25	12	10
06241-065	steel	light grey RAL 7035	M6	25	14	23	25	12	10
06241-063	steel	blue RAL5017	M6	25	14	23	25	12	10
06241-081	steel	orange RAL 2004	M8	33	18	31	33	15	14
06241-082	steel	signal green RAL6032	M8	33	18	31	33	15	14
06241-083	steel	blue RAL5017	M8	33	18	31	33	15	14
06241-085	steel	light grey RAL 7035	M8	33	18	31	33	15	14
06241-086	steel	traffic red RAL 3020	M8	33	18	31	33	15	14
06241-08	steel	black grey RAL 7021	M8	33	18	31	33	15	14
06241-087	steel	colza yellow RAL 1021	M8	33	18	31	33	15	14