

Item description/product images



Description

Material:

Steel.

Version:

Electro zinc-plated.

Note:


*A in mm by housing length H=18 mm, H=30 mm and H=50 mm.

Accessory:

Quarter-turn lock zinc, lockable 05564-10.

quarter-turn lock zinc, lockable, long version 05564-14.

Drawings



Overview of items

Order No.	Version 2	A for housing length H=18	A for housing length H=30	A for housing length H=50	B	B1	L
05564-15-13506	offset upwards	6	18	38	19	8,1	35
05564-15-13508	offset upwards	8	20	40	19	8,1	35
05564-15-13510	offset upwards	10	22	42	19	8,1	35
05564-15-13513	offset upwards	13	25	45	19	8,1	35
05564-15-13514	offset upwards	14	26	46	19	8,1	35
05564-15-13516	offset upwards	16	28	48	19	8,1	35
05564-15-13518	straight	18	30	50	19	8,1	35
05564-15-13520	offset downwards	20	32	52	19	8,1	35
05564-15-13522	offset downwards	22	34	54	19	8,1	35
05564-15-13524	offset downwards	24	36	56	19	8,1	35
05564-15-13526	offset downwards	26	38	58	19	8,1	35
05564-15-13528	offset downwards	28	40	60	19	8,1	35
05564-15-14504	offset upwards	4	16	36	19	8,1	45
05564-15-14506	offset upwards	6	18	38	19	8,1	45
05564-15-14508	offset upwards	8	20	40	19	8,1	45
05564-15-14510	offset upwards	10	22	42	19	8,1	45
05564-15-14513	offset upwards	13	25	45	19	8,1	45
05564-15-14514	offset upwards	14	26	46	19	8,1	45
05564-15-14516	offset upwards	16	28	48	19	8,1	45
05564-15-14518	straight	18	30	50	19	8,1	45
05564-15-14520	offset downwards	20	32	52	19	8,1	45
05564-15-14522	offset downwards	22	34	54	19	8,1	45
05564-15-14524	offset downwards	24	36	56	19	8,1	45
05564-15-14526	offset downwards	26	38	58	19	8,1	45
05564-15-14528	offset downwards	28	40	60	19	8,1	45
05564-15-14530	offset downwards	30	42	62	19	8,1	45
05564-15-14532	offset downwards	32	44	64	19	8,1	45
05564-15-14534	offset downwards	34	46	66	19	8,1	45
05564-15-14536	offset downwards	36	48	68	19	8,1	45
05564-15-14538	offset downwards	38	50	70	19	8,1	45
05564-15-14540	offset downwards	40	52	72	19	8,1	45
05564-15-14542	offset downwards	42	54	74	19	8,1	45