


Item description/product images



Description

Material:


Black thermoplastic.

Bush grade 5.8 steel or 1.4305 stainless steel.

Version:

Steel trivalent blue passivated, stainless steel bright.

Drawings



Overview of items

Order No.	Component material	Colour Cap	D	D1	D2	D3	H	H1	H2	T
06245-106	steel	black grey RAL 7021	M6	25	12	17	25	3	2	10
06245-1061	steel	orange RAL 2004	M6	25	12	17	25	3	2	10
06245-1062	steel	signal green RAL 6032	M6	25	12	17	25	3	2	10
06245-1063	steel	blue RAL5017	M6	25	12	17	25	3	2	10
06245-1065	steel	light grey RAL 7035	M6	25	12	17	25	3	2	10
06245-1066	steel	traffic red RAL 3020	M6	25	12	17	25	3	2	10
06245-1067	steel	colza yellow RAL 1021	M6	25	12	17	25	3	2	10
06245-208	steel	black grey RAL 7021	M8	32	15,5	19	33	3,5	2,6	14
06245-2081	steel	orange RAL 2004	M8	32	15,5	19	33	3,5	2,6	14
06245-2082	steel	signal green RAL 6032	M8	32	15,5	19	33	3,5	2,6	14
06245-2083	steel	blue RAL5017	M8	32	15,5	19	33	3,5	2,6	14
06245-2085	steel	light grey RAL 7035	M8	32	15,5	19	33	3,5	2,6	14
06245-2086	steel	traffic red RAL 3020	M8	32	15,5	19	33	3,5	2,6	14
06245-2087	steel	colza yellow RAL 1021	M8	32	15,5	19	33	3,5	2,6	14
06245-310	steel	black grey RAL 7021	M10	40	19	23	41	4	3	14
06245-3101	steel	orange RAL 2004	M10	40	19	23	41	4	3	14
06245-3102	steel	signal green RAL 6032	M10	40	19	23	41	4	3	14
06245-3103	steel	blue RAL5017	M10	40	19	23	41	4	3	14
06245-3105	steel	light grey RAL 7035	M10	40	19	23	41	4	3	14
06245-3106	steel	traffic red RAL 3020	M10	40	19	23	41	4	3	14
06245-3107	steel	colza yellow RAL 1021	M10	40	19	23	41	4	3	14
06245-410	steel	black grey RAL 7021	M10	50	24	31	51	5,5	4,5	14
06245-4101	steel	orange RAL 2004	M10	50	24	31	51	5,5	4,5	14

Overview of items

Order No.	Component material	Colour Cap	D	D1	D2	D3	H	H1	H2	T
06245-4102	steel	signal green RAL 6032	M10	50	24	31	51	5,5	4,5	14
06245-4103	steel	blue RAL5017	M10	50	24	31	51	5,5	4,5	14
06245-4105	steel	light grey RAL 7035	M10	50	24	31	51	5,5	4,5	14
06245-4106	steel	traffic red RAL 3020	M10	50	24	31	51	5,5	4,5	14
06245-4107	steel	colza yellow RAL 1021	M10	50	24	31	51	5,5	4,5	14
06245-412	steel	black grey RAL 7021	M12	50	24	31	51	5,5	4,5	18
06245-4121	steel	orange RAL 2004	M12	50	24	31	51	5,5	4,5	18
06245-4122	steel	signal green RAL 6032	M12	50	24	31	51	5,5	4,5	18
06245-4123	steel	blue RAL5017	M12	50	24	31	51	5,5	4,5	18
06245-4125	steel	light grey RAL 7035	M12	50	24	31	51	5,5	4,5	18
06245-4126	steel	traffic red RAL 3020	M12	50	24	31	51	5,5	4,5	18
06245-4127	steel	colza yellow RAL 1021	M12	50	24	31	51	5,5	4,5	18
06245-0106	stainless steel	black grey RAL 7021	M6	25	12	17	25	3	2	10
06245-01061	stainless steel	orange RAL 2004	M6	25	12	17	25	3	2	10
06245-01062	stainless steel	signal green RAL 6032	M6	25	12	17	25	3	2	10
06245-01063	stainless steel	blue RAL5017	M6	25	12	17	25	3	2	10
06245-01065	stainless steel	light grey RAL 7035	M6	25	12	17	25	3	2	10
06245-01066	stainless steel	traffic red RAL 3020	M6	25	12	17	25	3	2	10
06245-01067	stainless steel	colza yellow RAL 1021	M6	25	12	17	25	3	2	10
06245-0208	stainless steel	black grey RAL 7021	M8	32	15,5	19	33	3,5	2,6	14
06245-02081	stainless steel	orange RAL 2004	M8	32	15,5	19	33	3,5	2,6	14
06245-02082	stainless steel	signal green RAL 6032	M8	32	15,5	19	33	3,5	2,6	14
06245-02083	stainless steel	blue RAL5017	M8	32	15,5	19	33	3,5	2,6	14
06245-02085	stainless steel	light grey RAL 7035	M8	32	15,5	19	33	3,5	2,6	14
06245-02086	stainless steel	traffic red RAL 3020	M8	32	15,5	19	33	3,5	2,6	14
06245-02087	stainless steel	colza yellow RAL 1021	M8	32	15,5	19	33	3,5	2,6	14
06245-0310	stainless steel	black grey RAL 7021	M10	40	19	23	41	4	3	14
06245-03101	stainless steel	orange RAL 2004	M10	40	19	23	41	4	3	14
06245-03102	stainless steel	signal green RAL 6032	M10	40	19	23	41	4	3	14
06245-03103	stainless steel	blue RAL5017	M10	40	19	23	41	4	3	14
06245-03105	stainless steel	light grey RAL 7035	M10	40	19	23	41	4	3	14
06245-03106	stainless steel	traffic red RAL 3020	M10	40	19	23	41	4	3	14
06245-03107	stainless steel	colza yellow RAL 1021	M10	40	19	23	41	4	3	14
06245-0410	stainless steel	black grey RAL 7021	M10	50	24	31	51	5,5	4,5	14
06245-04101	stainless steel	orange RAL 2004	M10	50	24	31	51	5,5	4,5	14
06245-04102	stainless steel	signal green RAL 6032	M10	50	24	31	51	5,5	4,5	14
06245-04103	stainless steel	blue RAL5017	M10	50	24	31	51	5,5	4,5	14
06245-04105	stainless steel	light grey RAL 7035	M10	50	24	31	51	5,5	4,5	14
06245-04106	stainless steel	traffic red RAL 3020	M10	50	24	31	51	5,5	4,5	14
06245-04107	stainless steel	colza yellow RAL 1021	M10	50	24	31	51	5,5	4,5	14
06245-0412	stainless steel	black grey RAL 7021	M12	50	24	31	51	5,5	4,5	18
06245-04121	stainless steel	orange RAL 2004	M12	50	24	31	51	5,5	4,5	18
06245-04122	stainless steel	signal green RAL 6032	M12	50	24	31	51	5,5	4,5	18
06245-04123	stainless steel	blue RAL5017	M12	50	24	31	51	5,5	4,5	18
06245-04125	stainless steel	light grey RAL 7035	M12	50	24	31	51	5,5	4,5	18
06245-04126	stainless steel	traffic red RAL 3020	M12	50	24	31	51	5,5	4,5	18
06245-04127	stainless steel	colza yellow RAL 1021	M12	50	24	31	51	5,5	4,5	18