

Item description/product images



Description

Material:

Steel or 1.4305 stainless steel.

Version:



Trivalent passivated.

Stainless steel version bright.

Note:

LH thread refers to dimension D2.

Drawings

Form C
without circlipForm CS
with circlip

Overview of items

Order No.	Version 2	Form	Main material	D1	D2	D3	D4	A	L2	L3	E	SW
27650-0805	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	C	0.0019	8	M5	8	M5	22	10,2	9	10,2	7
27650-1006	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	C	0.0019	10	M6	10	M6	25	12,5	11	11,5	8
27650-1308	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	C	0.0019	13	M8	13	M8	30	16,5	13	14	11
27650-1610	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	C	0.0019	16	M10	16	M10	35	20	16	15,5	13
27650-1612	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	C	0.0019	16	M12	16	M12	35	20	16	15,5	13
27650-1914	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	C	0.0019	19	M14x1,5	22	M14x1,5	45	28	20	21,5	16
27650-1916	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	C	0.0019	19	M16	22	M16	45	28	20	21,5	16
27650-080501	Base / magnet 245012 Assembly / Clamping joint 240021 Fixing element / dial gauge holder 246038	C	0.0019	8	M5	8	M5	22	10,2	9	10,2	7
27650-100601	Base / magnet 245012 Assembly / Clamping joint 240021 Fixing element / dial gauge holder 246038	C	0.0019	10	M6	10	M6	25	12,5	11	11,5	8
27650-130801	Base / magnet 245012	C	0.0019	13	M8	13	M8	30	16,5	13	14	11

Overview of items

Order No.	Version 2	Form	Main material	D1	D2	D3	D4	A	L2	L3	E	SW
	Assembly / Clamping joint 240021 Fixing element / dial gauge holder 246038											
27650-161001	Base / magnet 245012 Assembly / Clamping joint 240021 Fixing element / dial gauge holder 246038	C	0.0019	16	M10	16	M10	35	20	16	15,5	13
27650-161201	Base / magnet 245012 Assembly / Clamping joint 240021 Fixing element / dial gauge holder 246038	C	0.0019	16	M12	16	M12	35	20	16	15,5	13
27650-191401	Base / magnet 245012 Assembly / Clamping joint 240021 Fixing element / dial gauge holder 246038	C	0.0019	19	M14x1,5	22	M14x1,5	45	28	20	21,5	16
27650-191601	Base / magnet 245012 Assembly / Clamping joint 240021 Fixing element / dial gauge holder 246038	C	0.0019	19	M16	22	M16	45	28	20	21,5	16
27650-080351	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	CS	0.0019	8	M3,5	8	M4	18	10,2	9	8	7
27650-08051	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	CS	0.0019	8	M5	8	M5	22	10,2	9	10,2	7
27650-10061	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	CS	0.0019	10	M6	10	M6	25	12,5	11	11,5	8
27650-13081	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	CS	0.0019	13	M8	13	M8	30	16,5	13	14	11
27650-16101	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	CS	0.0019	16	M10	16	M10	35	20	16	15,5	13
27650-16121	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	CS	0.0019	16	M12	16	M12	35	20	16	15,5	13
27650-19141	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	CS	0.0019	19	M14x1,5	22	M14x1,5	45	28	20	21,5	16
27650-19161	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	CS	0.0019	19	M16	22	M16	45	28	20	21,5	16
27650-080511	Base / magnet 245012 Assembly / Clamping joint 240021 Fixing element / dial gauge holder 246038	CS	0.0019	8	M5	8	M5	22	10,2	9	10,2	7
27650-100611	Base / magnet 245012 Assembly / Clamping joint 240021 Fixing element / dial gauge holder 246038	CS	0.0019	10	M6	10	M6	25	12,5	11	11,5	8
27650-130811	Base / magnet 245012 Assembly / Clamping joint 240021 Fixing element / dial gauge holder 246038	CS	0.0019	13	M8	13	M8	30	16,5	13	14	11
27650-161011	Base / magnet 245012 Assembly / Clamping joint 240021 Fixing element / dial gauge holder 246038	CS	0.0019	16	M10	16	M10	35	20	16	15,5	13
27650-161211	Base / magnet 245012 Assembly / Clamping joint 240021 Fixing element / dial gauge holder 246038	CS	0.0019	16	M12	16	M12	35	20	16	15,5	13
27650-191411	Base / magnet 245012 Assembly / Clamping joint 240021 Fixing element / dial gauge holder 246038	CS	0.0019	19	M14x1,5	22	M14x1,5	45	28	20	21,5	16
27650-191611	Base / magnet 245012 Assembly / Clamping joint 240021 Fixing element / dial gauge holder 246038	CS	0.0019	19	M16	22	M16	45	28	20	21,5	16
27650-08052	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	CS	22012-10321	8	M5	8	M5	22	10,2	9	10,2	7
27650-10062	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	CS	22012-10321	10	M6	10	M6	25	12,5	11	11,5	8
27650-13082	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	CS	22012-10321	13	M8	13	M8	30	16,5	13	14	11
27650-16102	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	CS	22012-10321	16	M10	16	M10	35	20	16	15,5	13

Overview of items

Order No.	Version 2	Form	Main material	D1	D2	D3	D4	A	L2	L3	E	SW
27650-16122	Base / magnet 245012 Assembly / Clamping joint 240011 Fixing element / dial gauge holder 246028	CS	22012-10321	16	M12	16	M12	35	20	16	15,5	13
27650-080521	Base / magnet 245012 Assembly / Clamping joint 240021 Fixing element / dial gauge holder 246038	CS	22012-10321	8	M5	8	M5	22	10,2	9	10,2	7
27650-100621	Base / magnet 245012 Assembly / Clamping joint 240021 Fixing element / dial gauge holder 246038	CS	22012-10321	10	M6	10	M6	25	12,5	11	11,5	8
27650-130821	Base / magnet 245012 Assembly / Clamping joint 240021 Fixing element / dial gauge holder 246038	CS	22012-10321	13	M8	13	M8	30	16,5	13	14	11
27650-161021	Base / magnet 245012 Assembly / Clamping joint 240021 Fixing element / dial gauge holder 246038	CS	22012-10321	16	M10	16	M10	35	20	16	15,5	13
27650-161221	Base / magnet 245012 Assembly / Clamping joint 240021 Fixing element / dial gauge holder 246038	CS	22012-10321	16	M12	16	M12	35	20	16	15,5	13