

Item description/product images



black grey RAL 7021	pure orange RAL 2004	signal green RAL 6032	traffic blue RAL 5017
light grey RAL 7035	traffic red RAL 3020	colza yellow RAL 1021	

Description

Material:

Knurled knob thermoplastic.
Washer aluminium.

Version:

Aluminium black anodised.

Note:


The arrow is engraved after anodizing. The set screw secures both the hub and the pressed-in washer. The H7 hole in the hub ensures a good tight fit on the shaft.

Δ Add the desired cap colour here. No colour code is required for black grey caps.

Drawing reference:

1) set screw

Drawings



Overview of items

Order No.	Colour Cap	D	D1	D2	D3	D4	H	H1	H2	H3	T
06105-105	5-Axis Shoulder Screw	5	21	32	19	M3	26,5	12,5	7,5	4,5	17
06105-1051	Built-in version	5	21	32	19	M3	26,5	12,5	7,5	4,5	17
06105-1052	light spring force	5	21	32	19	M3	26,5	12,5	7,5	4,5	17
06105-1053	Linear Actuator	5	21	32	19	M3	26,5	12,5	7,5	4,5	17
06105-1055	black	5	21	32	19	M3	26,5	12,5	7,5	4,5	17
06105-1056	750X75000 (+/- 10 mm)	5	21	32	19	M3	26,5	12,5	7,5	4,5	17
06105-1057	8 x ModuLine ML-20-6 ball joint Art. 241211, 1 x ML-40 ball joint Art. 241227 20 x extension ModuLine ML-20-50 Art. 245800, 4 x swivel joint ModuLine TurnStop ML-100 Art. 241200, 4 x function head ModuLine ML-20 Art. 245700	5	21	32	19	M3	26,5	12,5	7,5	4,5	17
06105-206	5-Axis Shoulder Screw	6	26	40	23	M4	31,5	15	9,5	5,5	20,5
06105-2061	Built-in version	6	26	40	23	M4	31,5	15	9,5	5,5	20,5

Overview of items

Order No.	Colour Cap	D	D1	D2	D3	D4	H	H1	H2	H3	T
06105-2062	light spring force	6	26	40	23	M4	31,5	15	9,5	5,5	20,5
06105-2063	Linear Actuator	6	26	40	23	M4	31,5	15	9,5	5,5	20,5
06105-2065	black	6	26	40	23	M4	31,5	15	9,5	5,5	20,5
06105-2066	750X75000 (+/- 10 mm)	6	26	40	23	M4	31,5	15	9,5	5,5	20,5
06105-2067	8 x ModuLine ML-20-6 ball joint Art. 241211, 1 x ML-40 ball joint Art. 241227 20 x extension ModuLine ML-20-50 Art. 245800, 4 x swivel joint ModuLine TurnStop ML-100 Art. 241200, 4 x function head ModuLineML-20 Art. 245700	6	26	40	23	M4	31,5	15	9,5	5,5	20,5
06105-308	5-Axis Shoulder Screw	8	34	52	31	M4	43	20	12	7	22
06105-3081	Built-in version	8	34	52	31	M4	43	20	12	7	22
06105-3082	light spring force	8	34	52	31	M4	43	20	12	7	22
06105-3083	Linear Actuator	8	34	52	31	M4	43	20	12	7	22
06105-3085	black	8	34	52	31	M4	43	20	12	7	22
06105-3086	750X75000 (+/- 10 mm)	8	34	52	31	M4	43	20	12	7	22
06105-3087	8 x ModuLine ML-20-6 ball joint Art. 241211, 1 x ML-40 ball joint Art. 241227 20 x extension ModuLine ML-20-50 Art. 245800, 4 x swivel joint ModuLine TurnStop ML-100 Art. 241200, 4 x function head ModuLineML-20 Art. 245700	8	34	52	31	M4	43	20	12	7	22