

Item description/product images

**Description****Material:**

Steel version:

Threaded sleeve steel.

Indexing pin steel.

Grip fibreglass reinforced thermoplastic PPA (high temperature resistant).

Version:

Steel version:

threaded sleeve, black oxidised.

Indexing pin hardened, ground and black oxidised.

Handle black grey RAL7021.

Note:

Indexing plungers are used where it is necessary to prevent changes of position due to lateral forces. A new locking position can be set only after the plunger has been manually disengaged. With this indexing plunger a cam lever is used to retract the pin. The indexing plunger remains unlocked as long as the handle is positioned over the dead-centre of the cam.

The ergonomic cam lever enables light handling with low effort.

Temperature range:

Permanent operating temperature acc. to IEC 216 max. 160°C.

Short-term operating temperature max. 250°C.

Advantages:

Simple and quick operation.

Suitable for high temperature applications.

With integrated detent function.

On request:

Special versions.

Accessory:

Spacer rings 03089

Positioning bushes for indexing plunger 03099-50


Mounting brackets 03099

Drawing reference:

Form A: without locknut

Form B: with locknut

Drawings



Overview of items

Order No.	Main material	Component colour	Form	Locknut	A	A1	B	B1	D	D1	Travel S	L	L1	L2	L3	SW1	SW2	Fx30°	Spring force initial pressure F1 approx. N	Spring force final pressure F2 approx. N
03090-8105A10.0069		9-pin	A	normally open contact	31,7	41,7	17,9	12,9	53/8	24	5	39	17	7	15	13	-	1,3	5	12
03090-8206A10.0069		9-pin	A	normally open contact	31,6	41,7	17,9	12,9	61/2	13	6	44	20	8	17	14	-	1,8	6	14
03090-8308A10.0069		9-pin	A	normally open contact	55,5	57,8	26,9	19,4	85/8	11	8	56,9	26	10	23	19	-	2,3	15	35
03090-8410A10.0069		9-pin	A	normally open contact	53,4	57,8	26,9	19,4	10/4	10	10	62,9	28	12	25	22	-	2,8	15	34
03090-9105A10.0069		9-pin	B	Clamping component set "Standard Type II" with storage box	31,7	41,7	17,9	12,9	53/8	24	5	39	17	7	15	13	17	1,3	5	12
03090-9206A10.0069		9-pin	B	Clamping component set "Standard Type II" with storage box	31,6	41,7	17,9	12,9	61/2	13	6	44	20	8	17	14	19	1,8	6	14
03090-9308A10.0069		9-pin	B	Clamping component set "Standard Type II" with storage box	55,5	57,8	26,9	19,4	85/8	11	8	56,9	26	10	23	19	24	2,3	15	35
03090-9410A10.0069		9-pin	B	Clamping component set "Standard Type II" with storage box	53,4	57,8	26,9	19,4	10/4	10	10	62,9	28	12	25	22	30	2,8	15	34